

# Product data sheet

Specifications



Contactor, TeSys K, 3P, AC-3  
<=440V 12A, 1NC aux., 110V DC  
low consumption coil

LC1K12016FLS207

## Main

Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LC1K
Device Application	Control
Contactor Application	Motor control Resistive load

## Complementary

Utilisation Category	AC-3 AC-3e AC-1 AC-4
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC <= 400 Hz Signalling circuit: <= 690 V AC <= 400 Hz
[Ie] Rated Operational Current	12 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 12 A (at <60 °C) at <= 440 V AC AC-3e for power circuit 20 A (at <60 °C) at <= 690 V AC AC-1 for power circuit
Control Circuit Type	DC low consumption
[Uc] Control Circuit Voltage	110 V DC
Motor Power Kw	3 kW at 220...230 V AC 50/60 Hz AC-3 5.5 kW at 380...415 V AC 50/60 Hz AC-3 5.5 kW at 440 V AC 50/60 Hz AC-3 4 kW at 690 V AC 50/60 Hz AC-3 3 kW at 220...230 V AC 50/60 Hz AC-3e 5.5 kW at 380...415 V AC 50/60 Hz AC-3e 5.5 kW at 440 V AC 50/60 Hz AC-3e 4 kW at 690 V AC 50/60 Hz AC-3e 3 kW at 220...230 V AC 50/60 Hz AC-4 5.5 kW at 380...415 V AC 50/60 Hz AC-4 5.5 kW at 440 V AC 50/60 Hz AC-4 4 kW at 690 V AC 50/60 Hz AC-4
Auxiliary Contact Composition	1 NC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit
Irms Rated Making Capacity	144 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Rated Breaking Capacity</b>	110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
<b>[Icw] Rated Short-Time Withstand Current</b>	115 A 50 °C - 1 s for power circuit 105 A 50 °C - 5 s for power circuit 100 A 50 °C - 10 s for power circuit 75 A 50 °C - 30 s for power circuit 55 A 50 °C - 1 min for power circuit 50 A 50 °C - 3 min for power circuit 25 A 50 °C - >= 15 min for power circuit 80 A - 1 s for signalling circuit 90 A - 500 ms for signalling circuit 110 A - 100 ms for signalling circuit
<b>Associated Fuse Rating</b>	25 A gG at <= 440 V for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660
<b>Average Impedance</b>	3 mOhm - lth 20 A 50 Hz for power circuit
<b>[Ui] Rated Insulation Voltage</b>	Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-5-1 Power circuit: 750 V conforming to VDE 0110 group C Power circuit: 690 V conforming to BS 5424 Power circuit: 690 V conforming to NF C 20-040
<b>Insulation Resistance</b>	> 10 MOhm for signalling circuit
<b>Inrush Power In W</b>	1.8 W (at 20 °C)
<b>Hold-In Power Consumption In W</b>	1.8 W at 20 °C
<b>Heat Dissipation</b>	1.8 W
<b>Control Circuit Voltage Limits</b>	Operational: 0.7...1.3 Uc (at <50 °C) Drop-out: >= 0.10 Uc (at <50 °C)
<b>Connections - Terminals</b>	Power circuit: lugs-ring terminals (external diameter: 7 mm)
<b>Maximum Operating Rate</b>	3600 cyc/h
<b>Coil Technology</b>	With integral suppression device
<b>Auxiliary Contacts Type</b>	type instantaneous 1 NC
<b>Signalling Circuit Frequency</b>	<= 400 Hz
<b>Minimum Switching Current</b>	5 mA for signalling circuit
<b>Minimum Switching Voltage</b>	17 V for signalling circuit
<b>Mounting Support</b>	Rail Plate
<b>Tightening Torque</b>	Power circuit: 0.8...1.3 N.m - on lugs-ring terminals - with screwdriver 3.2 mm flat Ø 6 mm Power circuit: 0.8...1.3 N.m - on lugs-ring terminals - with screwdriver 3.2 mm Philips No 2 Power circuit: 0.8...1.3 N.m - on lugs-ring terminals pozidriv No 2
<b>Operating Time</b>	10...20 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing
<b>Safety Reliability Level</b>	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
<b>Non Overlap Distance</b>	0.5 mm
<b>Mechanical Durability</b>	30 Mcycles
<b>Electrical Durability</b>	0.3 Mcycles 20 A AC-1 at Ue <= 440 V 1.3 Mcycles 12 A AC-3 at Ue <= 440 V

<b>Mechanical Robustness</b>	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6
<b>Height</b>	58 mm
<b>Width</b>	45 mm
<b>Depth</b>	57 mm
<b>Net Weight</b>	0.235 kg

## Environment

<b>Standards</b>	BS 5424 IEC 60947 NF C 63-110 VDE 0660 IEC 60077-1 IEC 60077-2 EN 45545: R22 HL3 EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
<b>Product Certifications</b>	CB Scheme CCC UL CSA EAC CE UKCA
<b>Ip Degree Of Protection</b>	IP20 conforming to VDE 0106
<b>Protective Treatment</b>	TC conforming to IEC 60068 TC conforming to DIN 50016
<b>Ambient Air Temperature For Storage</b>	-50...80 °C
<b>Permissible Ambient Air Temperature Around The Device</b>	-40...70 °C at Uc
<b>Operating Altitude</b>	2000 m without derating
<b>Flame Retardance</b>	V0 conforming to UL 94

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	5.7 cm
<b>Package 1 Width</b>	4.8 cm
<b>Package 1 Length</b>	6.2 cm
<b>Package 1 Weight</b>	240.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>