

Product data sheet

Specifications



TeSys Deca changeover contactor - 4P(4 NO) - AC-1 - <= 440 V 32 A - 110 V DC coil

LC2DT32FD

! Discontinued

Main

| | |
|---|--|
| Range | TeSys |
| Product Name | TeSys Deca |
| Product Or Component Type | Changeover contactor |
| Device Short Name | LC2D |
| Contactor Application | Resistive load |
| Utilisation Category | AC-1 AC-3 AC-3e AC-4 |
| Device Presentation | Preassembled, with prewired power connections |
| Poles Description | 4P |
| Power Pole Contact Composition | 4 NO |
| [Ue] Rated Operational Voltage | Power circuit: <= 690 V AC 25...400 Hz Power circuit: <= 300 V DC |
| [Ie] Rated Operational Current | 32 A (at <60 °C) at <= 440 V AC AC-1 for power circuit |
| Control Circuit Type | DC standard |
| [Uc] Control Circuit Voltage | 110 V DC |
| Auxiliary Contact Composition | 1 NO + 1 NC |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV conforming to IEC 60947 |
| Overvoltage Category | III |
| [Ith] Conventional Free Air Thermal Current | 10 A (at 60 °C) for signalling circuit 32 A (at 60 °C) for power circuit |
| Irms Rated Making Capacity | 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 300 A at 440 V for power circuit conforming to IEC 60947 |
| Rated Breaking Capacity | 300 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] Rated Short-Time Withstand Current | 40 A 40 °C - 10 min for power circuit 84 A 40 °C - 1 min for power circuit 145 A 40 °C - 10 s for power circuit 240 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit |
| Associated Fuse Rating | 10 A gG for signalling circuit conforming to IEC 60947-5-1 50 A gG at <= 690 V coordination type 1 for power circuit 35 A gG at <= 690 V coordination type 2 for power circuit |
| Average Impedance | 2.5 mOhm - Ith 32 A 50 Hz for power circuit |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------|--|
| [Ui] Rated Insulation Voltage | Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified |
| Electrical Durability | 1 Mcycles 32 A AC-1 at Ue <= 440 V |
| Power Dissipation Per Pole | 2.5 W AC-1 |
| Front Cover | With |
| Interlocking Type | Mechanical |
| Mounting Support | Rail Plate |
| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 |
| Product Certifications | LROS (Lloyds register of shipping) GOST BV CCC CSA DNV GL RINA UL |
| Connections - Terminals | Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²solid Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²solid Power circuit: connector 1 cable(s) 2.5...10 mm²flexible without cable end Power circuit: connector 2 cable(s) 2.5...10 mm²flexible without cable end Power circuit: connector 1 cable(s) 2.5...10 mm²flexible with cable end Power circuit: connector 2 cable(s) 2.5...10 mm²flexible with cable end Power circuit: connector 1 cable(s) 2.5...16 mm²solid Power circuit: connector 2 cable(s) 2.5...16 mm²solid |
| Tightening Torque | Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 1.7 N.m - on connector - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on connector - with screwdriver Philips No 2 |
| Operating Time | 53.55...72.45 ms closing 16...24 ms opening |
| Safety Reliability Level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical Durability | 30 Mcycles |
| Maximum Operating Rate | 3600 cyc/h 60 °C |

Complementary

| | |
|--------------------------------|--|
| Coil Technology | Built-in bidirectional peak limiting diode suppressor |
| Control Circuit Voltage Limits | 0.1...0.25 Uc (-40...70 °C):drop-out DC 0.7...1.25 Uc (-40...60 °C):operational DC 1...1.25 Uc (60...70 °C):operational DC |
| Time Constant | 28 ms |
| Inrush Power In W | 5.4 W (at 20 °C) |
| Hold-In Power Consumption In W | 5.4 W at 20 °C |

| | |
|------------------------------|--|
| Auxiliary Contacts Type | type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1 |
| Signalling Circuit Frequency | 25...400 Hz |
| Minimum Switching Current | 5 mA for signalling circuit |
| Minimum Switching Voltage | 17 V for signalling circuit |
| Non-Overlap Time | 1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact |
| Insulation Resistance | > 10 MOhm for signalling circuit |

Environment

| | |
|---------------------------------------|---|
| Ip Degree Of Protection | IP20 front face conforming to IEC 60529 |
| Climatic Withstand | conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D |
| Protective Treatment | TH conforming to IEC 60068-2-30 |
| Pollution Degree | 3 |
| Ambient Air Temperature For Operation | -40...60 °C 60...70 °C with derating |
| Ambient Air Temperature For Storage | -60...80 °C |
| Operating Altitude | 0...3000 m |
| Fire Resistance | 850 °C conforming to IEC 60695-2-1 |
| Flame Retardance | V1 conforming to UL 94 |
| Mechanical Robustness | Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 4 Gn, 5...300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms |
| Height | 91 mm |
| Width | 90 mm |
| Depth | 98 mm |
| Net Weight | 0.85 kg |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Pvc Free

Certifications & Standards

| | |
|-----------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |