


# Product data sheet

Specifications



## TeSys K reversing contactor , 3P , AC-3 <= 440 V 16 A , 1 NC , 12 V AC coil

LC2K16015J7

! Discontinued

### Main

Range	TeSys
Product Name	TeSys K
Product Or Component Type	Reversing contactor
Device Short Name	LC2K
Device Application	Control
Contactor Application	Motor control
Utilisation Category	AC-3 AC-4
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: 690 V AC 50/60 Hz Signalling circuit: <= 690 V AC 50/60 Hz
[Ie] Rated Operational Current	16 A at <= 440 V AC AC-3 for power circuit
Motor Power Kw	4 kW at 480 V AC 50/60 Hz 4 kW at 500...600 V AC 50/60 Hz 4 kW at 660...690 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz 4 kW at 220...230 V AC 50/60 Hz 7.5 kW at 380...415 V AC 50/60 Hz
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	12 V AC 50/60 Hz
Auxiliary Contact Composition	1 NC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	20 A (at 50 °C) for power circuit 10 A (at 50 °C) for signalling circuit
Irms Rated Making Capacity	160 A at 690 V AC for power circuit conforming to NF C 63-110 160 A at 690 V AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Icw] Rated Short-Time Withstand Current</b>	115 A 50 °C - 1 s for power circuit 105 A 50 °C - 5 s for power circuit 100 A 50 °C - 10 s for power circuit 75 A 50 °C - 30 s for power circuit 55 A 50 °C - 1 min for power circuit 50 A 50 °C - 3 min for power circuit 80 A - 1 s for signalling circuit 90 A - 500 ms for signalling circuit 110 A - 100 ms for signalling circuit 25 A 50 °C - >= 15 min for power circuit
<b>Associated Fuse Rating</b>	25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660
<b>Average Impedance</b>	3 mOhm - lth 20 A 50 Hz for power circuit
<b>[Ui] Rated Insulation Voltage</b>	Power circuit: 600 V conforming to UL 508 Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-5-1 Signalling circuit: 600 V conforming to UL 508 Power circuit: 600 V conforming to CSA C22.2 No 14 Signalling circuit: 600 V conforming to CSA C22.2 No 14
<b>Electrical Durability</b>	1.3 Mcycles 16 A AC-3 at Ue <= 440 V
<b>Interlocking Type</b>	Mechanical
<b>Mounting Support</b>	Rail Plate
<b>Standards</b>	EN/IEC 60947-4-1 EN/IEC 60947-5-1
<b>Product Certifications</b>	CB Scheme CCC UL CSA EAC CE UKCA
<b>Connections - Terminals</b>	Solder pins - busbar cross section: 1.5 x 0.9 mm
<b>Operating Time</b>	10...20 ms coil energisation and NO closing 10...20 ms coil de-energisation and NO opening
<b>Safety Reliability Level</b>	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
<b>Mechanical Durability</b>	5 Mcycles
<b>Maximum Operating Rate</b>	3600 cyc/h

## Complementary

<b>Control Circuit Voltage Limits</b>	Drop-out: 0.2...0.75 Uc (at <50 °C) Operational: 0.85...1.15 Uc (at <50 °C)
<b>Inrush Power In Va</b>	30 VA (at 20 °C)
<b>Hold-In Power Consumption In Va</b>	4.5 VA (at 20 °C)
<b>Heat Dissipation</b>	1.3 W
<b>Auxiliary Contacts Type</b>	type instantaneous 1 NC
<b>Signalling Circuit Frequency</b>	<= 400 Hz
<b>Minimum Switching Current</b>	5 mA for signalling circuit
<b>Minimum Switching Voltage</b>	17 V for signalling circuit
<b>Non Overlap Distance</b>	0.5 mm
<b>Insulation Resistance</b>	> 10 MOhm for signalling circuit

## Environment

Ip Degree Of Protection	IP20 conforming to VDE 0106
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-50...80 °C
Operating Altitude	2000 m without derating
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical Robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6
Height	58 mm
Width	90 mm
Depth	57 mm
Net Weight	0.39 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------