



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay to be ordered separately Contactor
Control type	Push-button reset blue R

Complementary

[Ie] rated operational current	9 A AC-3
Motor power kW	4 kW at 380/400 V AC 50/60 Hz 4 kW at 415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 2.2 kW at 220/230 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz 5.5 kW at 660/690 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	9 A
[Uc] control circuit voltage	380 V AC 50/60 Hz
Cable entry number	2 cable entry : ISO20 top 2 cable entry : ISO20 bottom 2 cable entry : Pg 13 bottom 2 cable entry : Pg 16 bottom
Width	88 mm
Height	166 mm
Depth	128.5 mm
Product weight	0.92 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Material	Polycarbonate
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------