



## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Neutral terminal Thermal overload relay to be ordered separately Contactor
Control type	Push-button start green I Push-button stop/reset red O

## Complementary

[I <sub>e</sub> ] rated operational current	12 A AC-3
Motor power kW	3 kW at 220/230 V AC 50/60 Hz 7.5 kW at 500 V AC 50/60 Hz 7.5 kW at 660/690 V AC 50/60 Hz 5.5 kW at 380/400 V AC 50/60 Hz 5.5 kW at 415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
[I <sub>th</sub> ] conventional enclosed thermal current	12 A
[U <sub>c</sub> ] control circuit voltage	42 V AC 50/60 Hz
Cable entry number	2 cable entry : ISO20 top 2 cable entry : ISO20 bottom 2 cable entry : Pg 13 bottom 2 cable entry : Pg 16 bottom
Width	88 mm
Height	166 mm
Depth	128.5 mm
Product weight	0.92 kg

## Environment

Material	Polycarbonate
----------	---------------

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

### Contractual warranty

Warranty period	18 months
-----------------	-----------