



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor
Control type	Push-button start green I Push-button stop/reset red O

Complementary

[Ie] rated operational current	50 A AC-3
Motor power kW	15 kW at 220/230 V AC 50/60 Hz 22 kW at 380/400 V AC 50/60 Hz 25 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz 30 kW at 500 V AC 50/60 Hz 33 kW at 660/690 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	50 A
[Uc] control circuit voltage	230 V AC 50/60 Hz
Cable entry number	3 1 Pg 13 + 2 Pg 29 bottom 3 1 ISO20 + 2 ISO32 bottom 2 1 Pg 13 + 1 Pg 29 top 2 1 ISO20 + 1 ISO32 top
Width	181 mm
Height	312 mm
Depth	161 mm
Net weight	4.85 kg

Environment

Material	Sheet steel
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty	18 months
----------	-----------

LE1D505P7 is replaced by:



DOL starters LE1D50AP7

TeSys LE - enclosed DOL starter - 50 A - 230 V AC coil

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017