



has not been replaced. Please contact your customer care center for more information.

## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor
Control type	Push-button reset blue R

## Complementary

[Ie] rated operational current	65 A AC-3
Motor power kW	30 kW at 380/400 V AC 50/60 Hz 37 kW at 415 V AC 50/60 Hz 37 kW at 440 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz 37 kW at 660/690 V AC 50/60 Hz 18.5 kW at 220/230 V AC 50/60 Hz
[I <sub>th</sub> e] conventional enclosed thermal current	65 A
[U <sub>c</sub> ] control circuit voltage	220 V AC 50/60 Hz
Cable entry number	3 1 Pg 13 + 2 Pg 29 bottom 3 1 ISO20 + 2 ISO32 bottom 2 1 Pg 13 + 1 Pg 29 top 2 1 ISO20 + 1 ISO32 top
Width	181 mm
Height	312 mm
Depth	161 mm
Net weight	4.85 kg

## Environment

Material	Sheet steel
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

### Contractual warranty

Warranty	18 months
----------	-----------