



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE2D
Product or component type	Enclosed DOL reversing starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Reversing contactor
[Ie] rated operational current	80 A AC-3
Motor power kW	22 kW at 220/230 V AC 50/60 Hz 37 kW at 380/400 V AC 50/60 Hz 45 kW at 415 V AC 50/60 Hz 45 kW at 440 V AC 50/60 Hz 45 kW at 660/690 V AC 50/60 Hz 55 kW at 500 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	80 A
[Uc] control circuit voltage	230 V AC 50/60 Hz
Control type	Push-button reset blue R

Complementary

Cable entry number	2 1 Pg 13 + 1 Pg 36 top 2 1 ISO20 + 1 ISO40 top 3 1 Pg 13 + 2 Pg 36 bottom 3 1 ISO20 + 2 ISO40 bottom
Width	367 mm
Height	287 mm
Depth	194 mm
Net weight	6.7 kg

Environment

Material	Sheet steel
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty	18 months
----------	-----------