



ⓘ Discontinued

LE4D656Q7A59 has not been replaced. Please contact your customer care center for more information.

Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Neutral terminal Fuse disconnecter Contactor
[Ie] rated operational current	65 A AC-3
Motor power kW	30 kW at 380/400 V AC 50/60 Hz 37 kW at 415 V AC 50/60 Hz 37 kW at 440 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz 37 kW at 660/690 V AC 50/60 Hz 18.5 kW at 220/230 V AC 50/60 Hz
[Uc] control circuit voltage	380 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	65 A
Associated fuse rating	80 A 22 x 58 mm aM
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	3 cable entry : 1 Pg 13 + 2 Pg 29 bottom 3 cable entry : 1 ISO20 + 2 ISO32 bottom 2 cable entry : 1 Pg 13 + 1 Pg 29 top 2 cable entry : 1 ISO20 + 1 ISO32 top
Width	367 mm
Height	195 mm
Depth	201 mm
Product weight	6.67 kg

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty period	18 months
-----------------	-----------