

# Product data sheet

Specifications



## TeSys LG - enclosed DOL starter - 6...10 A - 400 V AC coil

LG1K095V714

⚠ Discontinued on: Jun 27, 2020

⚠ Discontinued

### Main

Range	TeSys
Product Name	TeSys LG
Device Short Name	LG1K
Product Or Component Type	Enclosed DOL starter
Device Application	Safety
Utilisation Category	AC-3
Device Composition	Contactorswitch disconnectorcircuit-breaker
Motor Power Kw	4 kW at 400/415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 1.5 kW at 220/230 V AC 50/60 Hz
Thermal Protection Adjustment Range	6...10 A
[Uc] Control Circuit Voltage	400 V AC 50/60 Hz
Control Type	Push-button start white I Push-button stop black O Rotary handle emergency stop red

### Complementary

Cable Entry Number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	165 mm
Net Weight	1.12 kg

### Environment

Standards	IEC 60947-4-1 IEC 60204-1
Material	Polycarbonate
Ik Degree Of Protection	IK07 conforming to IEC 60529
Ip Degree Of Protection	IP55 conforming to IEC 60529
Environmental Characteristic	Standard environment

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	24.4 cm
Package 1 Length	17.5 cm
Package 1 Weight	1.42 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<b>Eu Rohs Directive</b>	Compliant	<a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>		<a href="#">China RoHS declaration</a>
<b>Weee</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	