

Product data sheet

Specifications



TeSys F - star delta starter - 3 x 3P (3 NO) - 225 A - 220/230 V AC coil

LC3F225M7

⚠ To be discontinued on: Jun 30, 2024

⚠ To be discontinued

Main

Range	TeSys
Product Name	TeSys F
Product Or Component Type	Star delta starter
Device Short Name	LC3F
Contactor Application	Motor control
Utilisation Category	AC-3
Device Presentation	Pre-wired
Poles Description	3 x 3P
Power Pole Contact Composition	3 x 3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 1000 V AC 16 Hz 2/3...200 Hz
[Ie] Rated Operational Current	225 A (at <55 °C) at <= 440 V AC AC-3 for power circuit
Motor Power Kw	100 kW at 220/230 V AC 50/60 Hz 200 kW at 380/400 V AC 50/60 Hz 200 kW at 415 V AC 50/60 Hz 220 kW at 440 V AC 50/60 Hz
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	220/230 V AC 50/60 Hz
Auxiliary Contact Composition	1 NC for KM1 star contactor 1 NO for KM1 star contactor 2 NC for KM2 line contactor 1 NO for KM2 line contactor 1 NC for KM3 delta contactor 2 NO for KM3 delta contactor
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Interlocking Type	Without start delta mechanical interlock
Mounting Support	Plate
Standards	JIS C8201-4-1 EN 60947-1 IEC 60947-1 EN 60947-4-1 IEC 60947-4-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CB
	CCC
	RMRoS
	DNV
	ABS
	LROS (Lloyds register of shipping)
	UL
	RINA
	CSA

Complementary

[Ith] Conventional Free Air Thermal Current	315 A 40 °C
Irms Rated Making Capacity	2250 A conforming to IEC 60947-4-1
Rated Breaking Capacity	1800 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1800 A 40 °C - 10 s 1000 A 40 °C - 30 s 850 A 40 °C - 1 min 560 A 40 °C - 3 min 440 A 40 °C - 10 min
Associated Fuse Rating	315 A gG at <= 440 V 250 A aM at <= 440 V
Connections - Terminals	Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: solid without cable end Power circuit: bar 2 - busbar cross section: 32 x 4 mm Power circuit: bolted connection Power circuit: lugs-ring terminals 1 185 mm² Power circuit: connector 1 185 mm²
Connections Bolt Diameter	M10
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 35 N.m
Operating Time	20...35 ms closing 7...15 ms opening
Mechanical Durability	10 Mcycles
Maximum Operating Rate	2400 cyc/h 55 °C
Starting Time	20 s
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc at 50/60 Hz (at <55 °C) Drop-out: 0.35...0.55 Uc at 50/60 Hz (at <55 °C)
Inrush Power In Va	805 VA 50 Hz cos phi 0.3 (at 20 °C) 970 VA 60 Hz cos phi 0.3 (at 20 °C)
Hold-In Power Consumption In Va	55 VA 50 Hz cos phi 0.3 (at 20 °C) 66 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	18...24 W
Width	525 mm
Height	110 mm
Depth	235 mm
Net Weight	16.5 kg

Environment

Ip Degree Of Protection	IP20 front face with shrouds conforming to IEC 60529 IP20 front face with shrouds conforming to VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Storage	-60...80 °C
Ambient Air Temperature For Operation	-5...55 °C -40...70 °C at Uc
Operating Altitude	3000 m without derating
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5...300 Hz Shocks contactor closed: 15 Gn for 11 ms Vibrations contactor closed: 5 Gn, 5...300 Hz Shocks contactor open: 7 Gn for 11 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	36.0 cm
Package 1 Width	66.0 cm
Package 1 Length	75.0 cm
Package 1 Weight	26.527 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information



Dimensions Drawings

Dimensions and Drawings

Chassis mounted starters

Pre-assembled: LC3 F185 to LC3 F400

For customer assembly: 2 x LC1 F●●● and 1 x LC1 D150 or 3 x LC1 F●●●



	a	b	c	G	H	K	K1	K2	K3	K4
LC3 F185 or 2 x LC1 F●●● + 1 x LC1 D with components F185	565	675	235	525	625	160	110	80	110	80
LC3 F225 or 3 x LC1 F●●● with components F225	565	675	235	525	625	160	110	80	110	80

	a	b	c	G	H	K	K1	K2	K3	K4
LC3 F265 or 3 x LC1 F●●● with components F265	665	775	266	625	725	165	110	100	110	110
LC3 F330 or 3 x LC1 F●●● with components F330	765	975	276	725	825	195	140	100	110	180
LC3 F400 or 3 x LC1 F●●● with components F400	765	975	276	725	925	195	140	100	180	110

Motor Starter BOM
Motor Starter BOM