

# Product data sheet

Specifications



## on mounting plate DOL starter - TeSys LC4-D - 25 A - coil 24 V AC

LC4D25AB7

⚠ Discontinued on: Nov 30, 2021

⚠ Discontinued

### Main

Range Of Product	TeSys
Device Short Name	LC4
Product Or Component Type	DOL starter
Motor Power Kw	11 kW at 380...400 V AC 50/60 Hz 11 kW at 415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 15 kW at 500 V AC 50/60 Hz 5.5 kW at 220...230 V AC 50/60 Hz
Utilisation Category	AC-3
[Ue] Rated Operational Voltage	24 V AC 50/60 Hz
[Ie] Rated Operational Current	25 A

### Complementary

Device Composition	Contacteur Fuse disconnecteur
Mounting Support	Plate
Width	86 mm
Height	173 mm
Depth	98 mm
Net Weight	1.58 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	10.5 cm
Package 1 Length	11 cm
Package 1 Weight	1.58 kg

### Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)