



### Main

Range	TeSys
Product name	TeSys Integral 63
Product or component type	Contactor breaker
Device short name	LD1LD

### Complementary

Utilisation category	AC-43
Poles description	3P
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ie] rated operational current	63 A AC AC-43
[Ith] conventional free air thermal current	63 A at $\leq 40$ °C
Motor power kW	30 kW at 400 V AC 50/60 Hz 33 kW at 415 V AC 50/60 Hz 55 kW at 660 V AC 50/60 Hz 15 kW at 220...240 V AC 50/60 Hz 33 kW at 440 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 60 Hz
Control type	Knob black front
Irms rated making capacity	946 A conforming to IEC 60947-4 756 A conforming to IEC 60947-4
[Ipk] rated peak withstand current	105 kA conforming to IEC 60947-2
Breaking capacity	Icu 10 kA at 600...690 V (cos $\phi$ 0.5) conforming to IEC 60947-2 Icu 30 kA at 480...525 V (cos $\phi$ 0.25) conforming to IEC 60947-6-2 Icu 50 kA at $\leq 440$ V (cos $\phi$ 0.25) conforming to IEC 60947-2
[Ics] rated service breaking capacity	10 kA at 600...690 V conforming to IEC 60947-2 35 kA at 480...525 V conforming to IEC 60947-2 50 kA at $\leq 440$ V conforming to IEC 60947-2
Maximum breaking time	$\leq 4$ ms
Thermal stress limit	300000 A <sup>2</sup> .s

[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-4
Control circuit voltage limits	0.25...0.7 Uc drop-out at <= 55 °C 0.85...1.1 Uc operation at <= 55 °C
[Ui] rated insulation voltage	690 V conforming to IEC 60947-1
Inrush power in VA	450 VA at 20 °C 60 Hz
Hold-in power consumption in VA	25 VA at 20 °C
Heat dissipation	11 W at 60 Hz for control circuit 5 W at 32 A per pole, hot state for power circuit 7 W at 50 A per pole, hot state for power circuit 9 W at 63 A per pole, hot state for power circuit 4.4 W at 25 A per pole, hot state for power circuit 5.8 W at 40 A per pole, hot state for power circuit
Operating time	12...35 ms AC network closing at 20 °C for control circuit 7...20 ms AC network opening at 20 °C for control circuit
Electrical durability	1 Mcycles on AC-3 - Icu 3 kA - at 415 V - after 1 cycle O-CO-r-CO at Isc 0.9 Mcycles on AC-3 - Icu 10 kA - at 415 V - after 1 cycle O-CO-r-CO at Isc 0.6 Mcycles on AC-3 - Icu 25 kA - at 415 V - after 1 cycle O-CO-r-CO at Isc 0.5 Mcycles on AC-3 - Icu 35 kA - at 415 V - after 1 cycle O-CO-r-CO at Isc 0.2 Mcycles on AC-3 - Icu 50 kA - at 415 V - after 1 cycle O-CO-r-CO at Isc
Mechanical durability	1.2 Mcycles
Connections - terminals	Power circuit : screw clamp terminals 1 cable 6...50 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 2 cable 6...25 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 1 cable 6...25 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 2 cable 6...25 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 1 cable 6...50 mm <sup>2</sup> - cable stiffness: solid
Tightening torque	Power circuit : 6 N.m - on screw clamp terminals
Width	90 mm
Height	243 mm
Depth	192 mm
Product weight	3.7 kg

## Environment

Standards	NF C 79-100 VDE 0170 VDE 471 IEC 60947-1 BS 4941 IEC 60158-1 NF C 63-130 IEC 60364 NF C 63-120 VDE 0171 NEN NF C 20-040 IEC 60947-4 IEC 60204-2 VDE 0660 BS 4752 VDE 0110 VDE 0113 BS 5424 NF C 63-650 NF C 63-110 IEC 60947-2 NBN VDE 0100 IEC 60204-1
Product certifications	SCC RINA LROS (Lloyds register of shipping) NKK CSA ASE OVE USSR SETI DNV

NEMKO  
GL  
DEMKO  
ASTA  
UL  
BV  
ASEFA

Protective treatment	TH
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C
Mechanical robustness	Vibrations de-energised state 3 Gn, 1...300 Hz Vibrations energised state 3 Gn, 1...300 Hz Shocks de-energised state 8 Gn for 11 ms Shocks energised state 8 Gn for 11 ms
IP degree of protection	IP20 B conforming to IEC 60144 IP20 B conforming to IEC 60529
Operating altitude	3000 m without derating

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0833 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------