



### Main

Product name	Wiser for KNX
Product or component type	Logic controller

### Complementary

Communication port protocol	BACnet Modbus IP (Internet Protocol) KNX
[Us] rated supply voltage	24 V DC
Power consumption in W	2 W
LED indicator	Green LED (CPU load) Green/red LED (KNX powered/reset)
Physical interface	1 x RJ45 1 x RS485 1 x RS232 1 x TP-UART2
Port Ethernet	10BASE-T/100BASE-TX
Integrated connection type	1 x USB 2.0 port
Control type	RESET push-button
Connections - terminals	KNX bus : bus terminal, 2 x 0.8 mm <sup>2</sup> Power supply : clamp terminal, 1.5 mm <sup>2</sup> Serial : clamp terminal, 1.5 mm <sup>2</sup>
Mounting support	DIN rail
Height	90 mm
Width	52 mm
Depth	58 mm

### Environment

Ambient air temperature for operation	-5...45 °C
Operating altitude	0...2000 m
Relative humidity	0...93 %
IP degree of protection	IP20
Directives	2002/96/EC - WEEE directive
Standards	IEC 60950-1

Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">End of Life Information</a>