



Main

Range	TeSys
Product name	TeSys Integral 63
Product or component type	Contactor breaker
Device short name	LD4LD

Complementary

Utilisation category	AC-1 AC-43
Poles description	3P
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ie] rated operational current	63 A AC AC-1 63 A AC AC-43
[Ith] conventional free air thermal current	63 A at $\leq 40\text{ }^{\circ}\text{C}$
Motor power kW	30 kW at 400 V AC 50/60 Hz 33 kW at 415 V AC 50/60 Hz 55 kW at 660 V AC 50/60 Hz 15 kW at 220...240 V AC 50/60 Hz 33 kW at 440 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Test function	Self test
Control type	Knob black front conforming to CNOMO Knob black front conforming to VDE 0113
Irms rated making capacity	946 A conforming to IEC 60947-4 756 A conforming to IEC 60947-4
[Ipk] rated peak withstand current	105 kA conforming to IEC 60947-2
Breaking capacity	Icu 10 kA at 600...690 V (cos f 0.5) conforming to IEC 60947-2 Icu 30 kA at 480...525 V (cos f 0.25) conforming to IEC 60947-6-2 Icu 50 kA at $\leq 440\text{ V}$ (cos f 0.25) conforming to IEC 60947-2
[Ics] rated service breaking capacity	10 kA at 600...690 V conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

35 kA at 480...525 V conforming to IEC 60947-2
 50 kA at <= 440 V conforming to IEC 60947-2

Maximum breaking time	<= 4 ms
Thermal stress limit	300000 A ² .s
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-4
Control circuit voltage limits	0.25...0.7 U _c drop-out at <= 55 °C 0.85...1.1 U _c operation at <= 55 °C
[U _i] rated insulation voltage	690 V conforming to IEC 60947-1
Inrush power in W	300 W at 20 °C
Hold-in power consumption in W	8 W at 20 °C
Heat dissipation	5 W at 32 A per pole, hot state for power circuit 7 W at 50 A per pole, hot state for power circuit 9 W at 63 A per pole, hot state for power circuit 4.4 W at 25 A per pole, hot state for power circuit 5.8 W at 40 A per pole, hot state for power circuit
Operating time	15...25 ms DC network opening at 20 °C for control circuit 25...40 ms DC network closing at 20 °C for control circuit
Electrical durability	1 Mcycles on AC-3 - I _{cu} 3 kA - at 415 V - after 1 cycle O-CO-r-CO at I _{sc} 0.9 Mcycles on AC-3 - I _{cu} 10 kA - at 415 V - after 1 cycle O-CO-r-CO at I _{sc} 0.6 Mcycles on AC-3 - I _{cu} 25 kA - at 415 V - after 1 cycle O-CO-r-CO at I _{sc} 0.5 Mcycles on AC-3 - I _{cu} 35 kA - at 415 V - after 1 cycle O-CO-r-CO at I _{sc} 0.2 Mcycles on AC-3 - I _{cu} 50 kA - at 415 V - after 1 cycle O-CO-r-CO at I _{sc}
Mechanical durability	1.2 Mcycles
Connections - terminals	Power circuit : screw clamp terminals 1 cable 6...50 mm ² - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 2 cable 6...25 mm ² - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 1 cable 6...25 mm ² - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 2 cable 6...25 mm ² - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 1 cable 6...50 mm ² - cable stiffness: solid
Tightening torque	Power circuit : 6 N.m - on screw clamp terminals
Width	90 mm
Height	243 mm
Depth	192 mm
Product weight	3.8 kg

Environment

Standards	BS 5424 IEC 60364 VDE 0100 IEC 60947-2 VDE 0113 VDE 0171 NF C 63-130 NF C 63-650 IEC 60947-4 NF C 63-110 NBN IEC 60158-1 IEC 60947-1 NF C 20-040 VDE 471 VDE 0110 NEN VDE 0170 NF C 63-120 BS 4752 NF C 79-100 IEC 60204-1 VDE 0660 IEC 60204-2 BS 4941
Product certifications	RINA OVE DNV UL NEMKO USSR

BV
 CSA
 SCC
 ASTA
 SETI
 ASE
 LROS (Lloyds register of shipping)
 ASEFA
 DEMKO
 NKK
 GL

Protective treatment	TH
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C
Mechanical robustness	Vibrations de-energised state 3 Gn, 1...300 Hz Vibrations energised state 3 Gn, 1...300 Hz Shocks de-energised state 8 Gn for 11 ms Shocks energised state 8 Gn for 11 ms
IP degree of protection	IP20 B conforming to IEC 60144 IP20 B conforming to IEC 60529
Operating altitude	3000 m without derating

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------