



Main

| | |
|-------------------------------------|---|
| Range | TeSys |
| Product name | TeSys LT |
| Product or component type | Electronic over current relay |
| Device short name | LT47 |
| Device application | Protection |
| Relay application | Overload $I_{max} > I_{setting}$ Sensitivity to phase failure Locked rotor, mechanical jamming $I > 3 \times I_{setting}$ |
| [Us] rated supply voltage | 24 V DC 24 V AC |
| Thermal protection adjustment range | 0.5...6 A |
| [Ui] rated insulation voltage | 600 V AC power circuit conforming to CSA 600 V AC power circuit conforming to UL 690 V AC power circuit conforming to IEC 60947-4-1 |

Complementary

| | |
|--|---|
| Network frequency | 50...60 Hz |
| Mounting support | Rail |
| Tripping threshold | 0.5...5 A |
| Electromagnetic compatibility | Conducted emission class A conforming to EN 55011 Immunity to electromagnetic interference 10 V/m conforming to IEC 61000-4-3 Resistance to electrostatic discharge 8 kV in open air conforming to IEC 61000-4-2 Resistance to electrostatic discharge 6 kV in direct mode conforming to IEC 61000-4-4 Immunity to fast transients 2 kV conforming to IEC 61000-4-4 Surge withstand 6 kV conforming to IEC 61000-4-5 Conducted HF disturbances 10 V conforming to IEC 61000-4-6 |
| Auxiliary contact composition | 1 NO + 1 NC |
| [I _{th}] conventional free air thermal current | 3 A for signalling circuit |
| Associated fuse rating | 3 A gG for signalling circuit 3 A BS for signalling circuit |
| [U _{imp}] rated impulse withstand voltage | 6 kV |
| Time range | 1...120 s - control type R-time 0.3...30 s - control type O-time |
| Local signalling | 1 LED (green) 1 LED (red) |

| | |
|-------------------------|--|
| Control type | Automatic for reset mode |
| Connections - terminals | Signalling circuit : lugs-ring terminals - external diameter: 7 mm Signalling circuit : screw clamp terminals 1 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end cable end Signalling circuit : screw clamp terminals 1 cable(s) 1...2.5 mm ² - cable stiffness: flexible - without cable end cable end Signalling circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end cable end Signalling circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - without cable end cable end |
| Tightening torque | Signalling circuit : 1.7 N.m screw : M3.5 |
| Height | 70.3 mm |
| Width | 71 mm |
| Depth | 77.2 mm |
| Product weight | 0.192 kg |

Environment

| | |
|---------------------------------------|---|
| Standards | IEC 60947 IEC 60255-6 |
| Product certifications | CSA UL |
| Protective treatment | TH conforming to IEC 60068 |
| IP degree of protection | IP20 conforming to VDE 0106 IP20 conforming to IEC 60529 |
| Ambient air temperature for operation | -25...60 °C without derating conforming to IEC 60947-4-1 |
| Ambient air temperature for storage | -30...80 °C |
| Operating altitude | 2000 m |
| Mechanical robustness | Shocks 15 Gn for 11 ms IEC 60068-2-7 Vibrations 4 gn IEC 60068-2-6 |
| Dielectric strength | 2 kV at 50 Hz conforming to IEC 60255-5 |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 0951 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|