

Product data sheet

Specifications



Standard control unit, TeSys Ultra,
3P, 8 to 32A, 690VAC, magnetic
protection, 24VAC coil

LUCL32B

Main

| | |
|--------------------------------------|---|
| Range | TeSys |
| Range Of Product | TeSys Ultra |
| Product Name | TeSys Ultra |
| Device Short Name | LUCL |
| Product Or Component Type | Magnetic control unit |
| Device Application | Motor control Motor protection |
| Product Specific Application | Protection of variable speed drive or soft startsoft stop unit |
| Main Function Available | Manual reset Short-circuit protection |
| Product Compatibility | Power base LUB32 Power base LUB38 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B32B |
| [Ue] Rated Operational Voltage | 690 V AC |
| Network Frequency | 40...60 Hz |
| Load Type | 3-phase motor - cooling: self-cooled |
| Utilisation Category | AC-43 AC-44 AC-41 |
| Motor Power Kw | 15 kW at 400...440 V AC 50/60 Hz 15 kW at 500 V AC 50/60 Hz 18.5 kW at 690 V AC 50/60 Hz |
| Rated Motor Current Adjustment Range | 8...32 A |
| Tripping Threshold | 14.2 x Ir +/- 20 % |
| [Uc] Control Circuit Voltage | 24 V AC |

Complementary

| | |
|--------------------------------|--|
| Control Circuit Voltage Limits | 20...26.5 V for AC circuit 24 V in operation 14.5 V for AC circuit 24 V drop-out |
| Typical Current Consumption | 220 mA at 24 V AC I maximum while closing with LUB32 220 mA at 24 V AC I maximum while closing with LUB38 90 mA at 24 V AC I rms sealed with LUB32 90 mA at 24 V AC I rms sealed with LUB38 |
| Heat Dissipation | 3 W for control circuit with LUB32 3 W for control circuit with LUB38 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|--|--|
| Operating Time | 35 ms opening with LUB32 for control circuit 35 ms opening with LUB38 for control circuit 70 ms closing with LUB32 for control circuit 70 ms closing with LUB38 for control circuit |
| Standards | EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier |
| Product Certifications | CE EAC ATEX |
| [Ui] Rated Insulation Voltage | 690 V conforming to IEC 60947-6-2 600 V conforming to UL 60947-4-1 600 V conforming to CSA C22.2 No 60947-4-1 |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV conforming to IEC 60947-6-2 |
| Safe Separation Of Circuit | 400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1 400 V SELV between the control or auxiliary circuit and the main circuit conforming to IEC 60947-1 |
| Fixing Mode | Plug-in (front face) |
| Width | 45 mm |
| Height | 66 mm |
| Depth | 60 mm |
| Net Weight | 0.135 kg |
| Compatibility Code | LUCL |

Environment

| | |
|---------------------------------------|--|
| Ip Degree Of Protection | IP20 front panel and wired terminals conforming to IEC 60947-1 IP20 other faces conforming to IEC 60947-1 IP40 front panel outside connection zone conforming to IEC 60947-1 |
| Protective Treatment | TH conforming to IEC 60068 |
| Ambient Air Temperature For Operation | -25...70 °C |
| Ambient Air Temperature For Storage | -40...85 °C |
| Operating Altitude | 2000 m |
| Fire Resistance | 960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12 |
| Shock Resistance | 10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27 |
| Vibration Resistance | 2 gn, 5...300 Hz, power poles open conforming to IEC 60068-2-6 4 gn, 5...300 Hz, power poles closed conforming to IEC 60068-2-6 |
| Resistance To Electrostatic Discharge | 8 kV level 3 in open air conforming to IEC 61000-4-2 8 kV level 4 on contact conforming to IEC 61000-4-2 |
| Non-Dissipating Shock Wave | 1 kV serial mode conforming to IEC 60947-6-2 2 kV common mode conforming to IEC 60947-6-2 |
| Resistance To Radiated Fields | 10 V/m 3 conforming to IEC 61000-4-3 |
| Resistance To Fast Transients | 2 kV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4 |
| Immunity To Radioelectric Fields | 10 V conforming to IEC 61000-4-6 |
| Immunity To Microbreaks | 3 ms |
| Immunity To Voltage Dips | 70 % / 500 ms conforming to IEC 61000-4-11 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.5 cm |
| Package 1 Width | 8.0 cm |
| Package 1 Length | 10.0 cm |
| Package 1 Weight | 133.0 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 23 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 3.417 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|------------------------------------|-----|
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| ✓ | Pvc Free | |
| ✓ | Halogen Free Plastic Parts Product | |

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |