



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay to be ordered separately Contactor
Control type	Selector switch 3 positions automatic start/stop/manual start I-O-II Push-button reset blue R

### Complementary

[Ie] rated operational current	9 A AC-3
Motor power kW	4 kW at 380/400 V AC 50/60 Hz 4 kW at 415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 2.2 kW at 220/230 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz 5.5 kW at 660/690 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	9 A
[Uc] control circuit voltage	380 V AC 50/60 Hz
Cable entry number	2 cable entry : ISO20 top 2 cable entry : ISO20 bottom 2 cable entry : Pg 13 bottom 2 cable entry : Pg 16 bottom
Width	88 mm
Height	166 mm
Depth	135 mm
Product weight	0.92 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Material	Polycarbonate
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------