



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Neutral terminal Fuse disconnecter Contactor
[Ie] rated operational current	40 A AC-3
Motor power kW	11 kW at 220/230 V AC 50/60 Hz 22 kW at 415 V AC 50/60 Hz 22 kW at 440 V AC 50/60 Hz 22 kW at 500 V AC 50/60 Hz 30 kW at 660/690 V AC 50/60 Hz 18.5 kW at 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	400 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	40 A
Associated fuse rating	40 A 14 x 51 mm aM
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	2 cable entry : 1 ISO20 + 1 ISO25 top 3 cable entry : 1 Pg 13 + 2 Pg 21 bottom 3 cable entry : 1 ISO20 + 2 ISO25 bottom 2 cable entry : 1 Pg 13 + 1 Pg 21 top
Width	367 mm
Height	195 mm
Depth	201 mm
Product weight	5.77 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty period	18 months
-----------------	-----------