



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4K
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Contactor
[Ie] rated operational current	6 A AC-3
Motor power kW	3 kW at 440 V AC 50/60 Hz 1.5 kW at 220/230 V AC 50/60 Hz 2.2 kW at 380/400 V AC 50/60 Hz 2.2 kW at 415 V AC 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	6 A
Associated fuse rating	10 A 10 x 38 mm aM
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom 4 cable entry : ISO20 top 4 cable entry : ISO20 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Product weight	1.45 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
-------------------------	------------------------------

IK degree of protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0925 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------