



Main

Range	Compact
Product name	Compact NSX
Product or component type	Circuit breaker
Device short name	Compact NSX100F
Device application	Distribution
Poles description	3P
Protected poles description	3t
Network type	AC
Network frequency	50/60 Hz
[In] rated current	100 A at 40 °C
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	690 V AC 50/60 Hz
Breaking capacity code	F 36 kA 415 V AC
Breaking capacity	10 kA at 600 V AC 50/60 Hz conforming to UL 508 25 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 8 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	11 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 4 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 12.5 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Utilisation category	Category A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	LI
Pollution degree	3 conforming to IEC 60664-1

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Auxiliary contact composition	Without
Mechanical durability	50000 cycles
Electrical durability	10000 cycles 690 V In conforming to IEC 60947-2 20000 cycles 690 V In/2 conforming to IEC 60947-2 30000 cycles 440 V In conforming to IEC 60947-2 50000 cycles 440 V In/2 conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	Positive contact indication
Protection type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip unit rating	80 A at 40 °C
Long time pick-up adjustment type I _r	Adjustable
Long time pick-up adjustment range	0.7...1 x I _n
Long time delay adjustment type	Fixed
[Tr] long-time delay adjustment range	120...400 s at 1.5 x I _n 15 s at 6 x I _r
Short-time pick-up adjustment type I _{sd}	Fixed
[I _{sd}] short-time pick-up adjustment range	640 A
Short-time delay adjustment type	Fixed
Height	161 mm
Width	105 mm
Depth	86 mm
Net weight	2.05 kg
Compatibility code	NSX100

Environment

Overvoltage category	Class II
Electrical shock protection class	Class II
Standards	EN/IEC 60947 UL 508
Product certifications	CCC Marine EAC
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------