

Product data sheet

Specifications



Overload relay, TeSys LRD, motor protection, 22A to 110A, 3 phase, electronic thermal

LR9D110S

❗ Discontinued

Main

Range	TeSys
Product Name	TeSys LRD
Device Short Name	LR9D
Product Or Component Type	Electronic thermal overload relay
Relay Application	Motor protection
Product Compatibility	LC1D50A LC1D38 LC1D25 LC1D40A LC1D80 LC1D65A LC1D115 LC1D95 LC1D32
Thermal Overload Class	Class 5...30
Thermal Protection Adjustment Range	22...110 A
Power Consumption In W	300 mW
Mounting Support	Plate Rail

Complementary

[Ue] Rated Operational Voltage	690 V for power circuit 660 V for signalling circuit
[Ui] Rated Insulation Voltage	Power circuit: 1000 V Signalling circuit: 690 V
Tripping Threshold	1.25 In conforming to IEC 60947-4-1
Control Type	Red push-button: stop and manual reset White 2 microswitches: adjustable trip class Red knob: automatic reset White dial: full-load current adjustment
Time Range	1.5...4 min - automatic reset time
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
Associated Fuse Rating	5 A gG for signalling circuit 5 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Phase difference > 40% 3 s conforming to IEC 60947-4-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electromagnetic Compatibility	Surge withstand: 2 kV common mode conforming to IEC 61000-4-5 Resistance to electrostatic discharge: 8 kV conforming to IEC 61000-4-2 Immunity to radiated radio-electrical interference: 10 V/m conforming to IEC 61000-4-3 Immunity to fast transients: 2 kV conforming to IEC 61000-4-4
Connections - Terminals	Control circuit: screw clamp terminals 1 cable 2.5 mm² - cable stiffness: solid or flexible - without cable end Power circuit: screw clamp terminals 1 cable 50 mm² - cable stiffness: solid or flexible - without cable end
Tightening Torque	Control circuit: 0.8 N.m on screw clamp terminals Power circuit: 9 N.m on screw clamp terminals
Height	107 mm
Width	65 mm
Depth	79.9 mm
Net Weight	0.6 kg

Environment

Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5
Product Certifications	IECEE CB Scheme UL CSA CCC
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Ambient Air Temperature For Operation	-25...70 °C conforming to IEC 60255-8
Ambient Air Temperature For Storage	-55...80 °C
Operating Altitude	2000 m without derating
Mechanical Robustness	Vibrations 10...150 Hz: 6 Gn conforming to IEC 60068-2-6 Shocks 11 ms: 15 gn conforming to IEC 60068-2-7
Dielectric Strength	6 kV 50 Hz conforming to IEC 60255-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	12.1 cm
Package 1 Length	12.3 cm
Package 1 Weight	690.9 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov