

Product data sheet

Specifications



Extension module, TeSys T, 4 inputs, 24VDC, for LTMR controller

LTMEV40BD

Main

Range	TeSys
Product Name	TeSys T
Device Short Name	LTME
Product Or Component Type	Extension module
Device Application	Equipment monitoring and control
Range Compatibility	TeSys TeSys T LTMR motor controller
Supply	Via the controller

Complementary

[Ui] Rated Insulation Voltage	690 V conforming to EN/IEC 60947-1 690 V conforming to CSA C22.2 No 14 690 V conforming to UL 508
[Uimp] Rated Impulse Withstand Voltage	6 kV current or voltage measurement circuit conforming to EN/IEC 60947-4-1 0.8 kV supply, inputs and outputs conforming to EN/IEC 60947-4-1
Logic Input Number	4
Input Current	7 mA
Current State 0 Guaranteed	Logic input: < 5 V and <= 15 mA for 5 ms
Current State 1 Guaranteed	Logic input: < 15 V and 2...15 mA for 15 ms
Maximum Output Switching Frequency	2 Hz
Maximum Operating Rate	1800 cyc/h
Contacts Type And Composition	Without
Metering Type	Voltage U21, U32, U13, V1, V2, V3 Imbalance voltage Frequency Calculated active and reactive energy (+/- W.h, +/- VAR.h) Reactive power Q, Q1, Q2, Q3 Power factor Active power P, P1, P2, P3
Measurement Accuracy	1 % voltage (100...830 V) 3 % power factor 5 % active and reactive power
Overvoltage Category	III
Connection Pitch	5.08 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Control circuit: connector 1 cable(s) 0.25...2.5 mm² (AWG 24...AWG 14) flexible with cable end Control circuit: connector 1 cable(s) 0.2...2.5 mm² (AWG 24...AWG 14) flexible without cable end Control circuit: connector 1 cable(s) 0.25...2.5 mm² (AWG 24...AWG 14) flexible without cable end Control circuit: connector 1 cable(s) 0.2...2.5 mm² (AWG 24...AWG 14) solid without cable end Control circuit: connector 2 cable(s) 0.2...1 mm² (AWG 24...AWG 14) flexible with cable end Control circuit: connector 2 cable(s) 0.2...1.5 mm² (AWG 24...AWG 14) flexible without cable end Control circuit: connector 2 cable(s) 0.5...1.5 mm² (AWG 24...AWG 14) flexible without cable end Control circuit: connector 2 cable(s) 0.2...1 mm² (AWG 24...AWG 14) solid without cable end
Tightening Torque	Control circuit: 0.5...0.6 N.m flat screwdriver 3 mm
Pollution Degree	3
Electromagnetic Compatibility	Electrostatic discharge, 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Fast transients immunity test (other circuits), level 3, 2 kV, conforming to EN/IEC 61000-4-4 Fast transients immunity test (on supply and relay outputs), level 4, 4 kV, conforming to EN/IEC 61000-4-4 Conducted RF disturbances, 10 V, conforming to EN/IEC 61000-4-6 Control circuit: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (serial mode), 1 kV, conforming to EN/IEC 61000-4-5 Communication: surges (common mode), 2 kV, conforming to EN/IEC 61000-4-5 Voltage inputs: surges (serial mode), 2 kV, conforming to EN/IEC 61000-4-5 Voltage inputs: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5
Width	45 mm
Height	61 mm
Depth	120.7 mm
Net Weight	0.21 kg
Compatibility Code	LTME

Environment

Standards	IEC 60947-4-1 UL 508 EN 60947-4-1 IACS E10 CSA C22.2 No 14
Product Certifications	UL NOM ATEX BV CSA EAC RINA LROS (Lloyds register of shipping) DNV ABS GL KERI RMRoS C-Tick CCC
Ip Degree Of Protection	IP20
Protective Treatment	12 x 24 hour cycles conforming to EN/IEC 60068-2-30 48 h conforming to EN/IEC 60070-2-11 TH conforming to EN/IEC 60068
Fire Resistance	650 °C conforming to EN/IEC 60695-2-12 960 °C conforming to UL 94
Ambient Air Temperature For Operation	-20...60 °C

Ambient Air Temperature For Storage	-40...80 °C
Operating Altitude	<= 2000 m without derating
Mechanical Robustness	Shocks half sine wave acceleration: 15 Gn for 11 ms conforming to EN/IEC 60068-2-27 Vibrations mounted on symmetrical rail: 1 Gn, 5...300 Hz conforming to EN/IEC 60068-2-6 Vibrations plate mounted: 4 Gn, 5...300 Hz conforming to EN/IEC 60068-2-6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	7.2 cm
Package 1 Length	13.5 cm
Package 1 Weight	195.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.251 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information