

# Product data sheet

Specifications



Motor Management, TeSys T, motor controller, Profibus DP, 6 logic inputs, 3 logic outputs, 0.4 to 8A, 100 to 240VAC

LTMR08PFM

## Main

Range	TeSys
Product Name	TeSys T
Device Short Name	LTMR
Product Or Component Type	Motor controller
Device Application	Equipment monitoring and control
Measurement Current	0.4...8 A
[Us] Rated Supply Voltage	100...240 V AC 50/60 Hz
Current Consumption	8...62.8 mA
Supply Voltage Limits	93.5...264 V AC
Communication Port Protocol	Profibus DP
Bus Type	Profibus DP polarised 2-wire RS485 interface, addressing 1...125, transmission rate 9.6 kbit/s...12 Mbit/s, SUB-D 9 with 2 shielded twisted pairs, type A Profibus DP polarised 2-wire RS485 interface, addressing 1...125, transmission rate 9.6 kbit/s...12 Mbit/s, terminal block with 2 shielded twisted pairs, type A

## Complementary

[Ui] Rated Insulation Voltage	690 V conforming to EN/IEC 60947-1 690 V conforming to CSA C22.2 No 14 690 V conforming to UL 508
[Uimp] Rated Impulse Withstand Voltage	4 kV supply, inputs and outputs conforming to EN/IEC 60947-4-1 6 kV current or voltage measurement circuit conforming to EN/IEC 60947-4-1 0.8 kV communication circuit conforming to EN/IEC 60947-4-1
Short-Circuit Withstand	100 kA conforming to EN/IEC 60947-4-1
Associated Fuse Rating	4 A gG for output 0.5 A gG for control circuit
Protection Type	Locked rotor Overload Phase unbalance Phase failure Earth-leakage protection Reverse polarity protection Load fluctuation Thermal protection Power factor variation Thermal overload protection Overload (long time)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Network And Machine Diagnosis Type</b>	Phase fault and earth fault trip counters Trip history information Starting current and time Fault recording Waiting time after overload tripping Event recording Motor control command recording Running hours counter/operating time Trip context information Remaining operating time before overload tripping
<b>Logic Input Number</b>	6
<b>Input Current</b>	3.1 mA at 100 V 7.5 mA at 240 V
<b>Current State 0 Guaranteed</b>	Logic input: 0...40 V and $\leq 15$ mA for 25 ms
<b>Current State 1 Guaranteed</b>	Logic input: 79...264 V and $\geq 2$ mA for 25 ms
<b>Maximum Output Switching Frequency</b>	2 Hz
<b>Load Current</b>	5 A at 250 V AC for logic output 5 A at 30 V DC for logic output
<b>Permissible Power</b>	480 VA (AC-15), $I_e = 2$ A, 500000 cycles (output) 30 W (DC-13), $I_e = 1.25$ A, 500000 cycles (output)
<b>Maximum Operating Rate</b>	1800 cyc/h
<b>Contacts Type And Composition</b>	1 NO + 1 NC fault signal 3 NO
<b>Metering Type</b>	Average current $I_{avg}$ Earth-fault current Temperature Imbalance current Phase current $I_1, I_2, I_3$ RMS
<b>Measurement Accuracy</b>	5...15 % earth fault current internal measurement 1 % voltage (100...830 V) 3 % power factor 5 % earth fault current external measurement +/- 30 min/year internal clock 0,02 temperature 1 % current 5 % active and reactive power
<b>Overvoltage Category</b>	III
<b>Connection Pitch</b>	5.08 mm
<b>Connections - Terminals</b>	Control circuit: connector 1 cable(s) 0.25...2.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible with cable end Control circuit: connector 1 cable(s) 0.2...2.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 1 cable(s) 0.25...2.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 1 cable(s) 0.2...2.5 mm <sup>2</sup> (AWG 24...AWG 14) solid without cable end Control circuit: connector 2 cable(s) 0.2...1 mm <sup>2</sup> (AWG 24...AWG 14) flexible with cable end Control circuit: connector 2 cable(s) 0.2...1.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 2 cable(s) 0.5...1.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 2 cable(s) 0.2...1 mm <sup>2</sup> (AWG 24...AWG 14) solid without cable end
<b>Tightening Torque</b>	Control circuit: 0.5...0.6 N.m flat screwdriver 3 mm
<b>Pollution Degree</b>	3

Electromagnetic Compatibility	Electrostatic discharge, 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Radiated RF fields, 3, 10 V/m, conforming to EN/IEC 61000-4-3 Fast transients immunity test (other circuits), level 3, 2 kV, conforming to EN/IEC 61000-4-4 Fast transients immunity test (on supply and relay outputs), level 4, 4 kV, conforming to EN/IEC 61000-4-4 Voltage dips and interruptions immunity test, 70 %, 500 ms, conforming to EN/IEC 61000-4-11 Conducted RF disturbances, 10 V, conforming to EN/IEC 61000-4-6 Temperature sensor: surges (serial mode), 0.5 kV, conforming to EN/IEC 61000-4-5 Temperature sensor: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (serial mode), 1 kV, conforming to EN/IEC 61000-4-5 Communication: surges (common mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (serial mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (common mode), 2 kV, conforming to EN/IEC 61000-4-5
Width	91 mm
Height	61 mm
Depth	122.5 mm
Net Weight	0.53 kg
Web Services	Web server
Compatibility Code	LTMR

## Environment

Standards	UL 508 IEC 60947-4-1 EN 60947-4-1 IACS E10 CSA C22.2 No 14
Product Certifications	CSA C-Tick UL CCC LROS (Lloyds register of shipping) NOM ABS GL EAC BV DNV RINA RMRoS ATEX KERI
Protective Treatment	12 x 24 hour cycles conforming to EN/IEC 60068-2-30 48 h conforming to EN/IEC 60070-2-11 TH conforming to EN/IEC 60068
Fire Resistance	650 °C conforming to EN/IEC 60695-2-12 960 °C conforming to UL 94
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C
Operating Altitude	<= 2000 m without derating
Mechanical Robustness	Vibrations mounted on symmetrical rail: 1 Gn, 5...300 Hz conforming to EN/IEC 60068-2-6 Vibrations plate mounted: 4 Gn, 5...300 Hz conforming to EN/IEC 60068-2-6 Shocks half sine wave acceleration: 15 Gn for 11 ms conforming to EN/IEC 60068-2-27
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	10 cm
Package 1 Length	13.6 cm
Package 1 Weight	526 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.656 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>