



Main

| | |
|--|--|
| Range | Compact |
| Product name | Compact NSX |
| Product or component type | Circuit breaker |
| Device short name | Compact NSX160B |
| Device application | Distribution |
| Poles description | 3P |
| Protected poles description | 3t |
| Network type | AC |
| Network frequency | 50/60 Hz |
| [In] rated current | 160 A at 40 °C |
| [Ui] rated insulation voltage | 800 V AC 50/60 Hz |
| [Uimp] rated impulse withstand voltage | 8 kV |
| [Ue] rated operational voltage | 690 V AC 50/60 Hz |
| Breaking capacity code | B 25 kA 415 V AC |
| Breaking capacity | 15 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 |
| [Ics] rated service breaking capacity | 20 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 |
| Suitability for isolation | Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2 |
| Utilisation category | Category A |
| Trip unit name | TM-D |
| Trip unit technology | Thermal-magnetic |
| Trip unit protection functions | LI |
| Pollution degree | 3 conforming to IEC 60664-1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

| | |
|---|---|
| Control type | Toggle |
| Mounting mode | Fixed |
| Mounting support | Backplate |
| Upside connection | Front |
| Downside connection | Front |
| Mechanical durability | 40000 cycles |
| Electrical durability | 10000 cycles 440 V In/2 conforming to IEC 60947-2 15000 cycles 690 V In/2 conforming to IEC 60947-2 20000 cycles 440 V In conforming to IEC 60947-2 7500 cycles 690 V In conforming to IEC 60947-2 |
| Connection pitch | 35 mm |
| Local signalling | Positive contact indication |
| Protection type | L : for overload protection (thermal) I : for short-circuit protection (magnetic) |
| Trip unit rating | 160 A at 40 °C |
| Long time pick-up adjustment type Ir | Adjustable |
| Long time pick-up adjustment range | 0.7...1 x In |
| Long time delay adjustment type | Fixed |
| [Tr] long-time delay adjustment range | 120...400 s at 1.5 x In 15 s at 6 x Ir |
| Short-time pick-up adjustment type Isd | Fixed |
| [Isd] short-time pick-up adjustment range | 1250 A |
| Short-time delay adjustment type | Fixed |
| Height | 161 mm |
| Width | 105 mm |
| Depth | 86 mm |
| Net weight | 2.2 kg |
| Compatibility code | NSX160 |

Environment

| | |
|---------------------------------------|------------------------------|
| Overvoltage category | Class II |
| Electrical shock protection class | Class II |
| Standards | EN/IEC 60947 |
| Product certifications | EAC Marine CCC |
| IP degree of protection | IP40 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to IEC 62262 |
| Ambient air temperature for operation | -35...70 °C |
| Ambient air temperature for storage | -55...85 °C |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|
