

# Product data sheet

Specifications



Circuit breaker basic frame,  
ComPact NSX160N, 50kA at  
415VAC 50/60 Hz, 160A, without  
trip unit, 4 poles

LV430411

! Discontinued

! Discontinued on: Dec 25, 2023

Important message: This product has been switched to new  
ComPacT range and is no longer commercialized.

## Main

Range	ComPact
Range Of Product	ComPact NSX100...250
Device Short Name	NSX160N
Product Or Component Type	Basic frame
Device Application	Distribution
Circuit Breaker Name	Compact NSX160N
Number Of Poles	4P
Neutral Position	Left
[In] Rated Current	160 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	10 kA at 600 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508 10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 480 V AC 50/60 Hz conforming to UL 508 36 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 90 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	N 50 kA 415 V AC
Control Type	Toggle
Mounting Mode	Fixed

## Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Ics] Rated Service Short-Circuit Breaking Capacity</b>	10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 90 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
<b>Mechanical Durability</b>	40000 cycles conforming to IEC 60947-2
<b>Electrical Durability</b>	40000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 15000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 20000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 7500 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2
<b>Mounting Support</b>	Backplate
<b>Upside Connection</b>	Front
<b>Downside Connection</b>	Front
<b>Connection Pitch</b>	35 mm
<b>Protection Type</b>	Without protection
<b>Width (W)</b>	140 mm
<b>Height (H)</b>	161 mm
<b>Depth (D)</b>	86 mm

## Environment

<b>Standards</b>	EN/IEC 60947-2 UL 508
<b>Product Certifications</b>	UL CSA
<b>Pollution Degree</b>	3 conforming to IEC 60664-1
<b>Ip Degree Of Protection</b>	IP40 conforming to IEC 60529
<b>Ik Degree Of Protection</b>	IK07 conforming to IEC 62262
<b>Ambient Air Temperature For Operation</b>	-25...70 °C
<b>Ambient Air Temperature For Storage</b>	-50...85 °C

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	14.000 cm
<b>Package 1 Width</b>	14.500 cm
<b>Package 1 Length</b>	19.300 cm
<b>Package 1 Weight</b>	1.936 kg
<b>Unit Type Of Package 2</b>	S04
<b>Number Of Units In Package 2</b>	7
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	40.000 cm
<b>Package 2 Length</b>	60.000 cm
<b>Package 2 Weight</b>	14.150 kg

## Contractual warranty

Warranty

18 months

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>