



### Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	PowerPact B Compact NSXm
Voltage release type	Shunt trip
[Uc] control circuit voltage	110...130 V AC 125 V DC

### Complementary

Control signal type	Maintained Impulse
Impulse duration	$\geq 20$ ms
Threshold tripping voltage	$0.7 U_n$ - during opening time
Mounting mode	Clip-on
Response time	$< 50$ ms
Auxiliary connection terminal	Pre-wired $0...0.8$ mm <sup>2</sup> (AWG 18) stranded copper
Wire stripping length	8 mm
Cable length	1 m

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications