



Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	PowerPact B Compact NSXm
Voltage release type	Shunt trip
[Uc] control circuit voltage	220...240 V AC 208...240 V AC 250 V DC 277 V AC

Complementary

Control signal type	Impulse Maintained
Impulse duration	>= 20 ms
Threshold tripping voltage	0.7 Un - during opening time
Mounting mode	Clip-on
Response time	< 50 ms
Auxiliary connection terminal	Pre-wired 0...0.8 mm ² (AWG 18) stranded copper
Wire stripping length	8 mm
Cable length	1 m

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1824 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications