



### Main

Range of product	NSX100...250 NSX100...250 DC
Product or component type	Trip unit
Range compatibility	Compact NSX100 Compact NSX160 Compact NSX250 Compact NSX100 DC Compact NSX160 DC Compact NSX250 DC
Device application	Distribution
Poles description	4P
Protected poles description	4t
Neutral position	Left
Network type	AC DC
Network frequency	50/60 Hz
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	LI
Trip unit rating	25 A 40 °C
Protection type	Overload protection (thermal) L Short-circuit protection (magnetic) I

### Complementary

Mounting mode	Fixed
[Ue] rated operational voltage	690 V AC 50/60 Hz 750 V DC
Long time pick-up adjustment type Ir	Adjustable
Long time pick-up adjustment range	0.7...1 x In
Long time delay adjustment type	Fixed
[Tr] long-time delay adjustment range	120...400 s at 1.5 x In

15 s at 6 x Ir

Short-time pick-up adjustment type Isd	Fixed
[Isd] short-time pick-up adjustment range	300
Short-time delay adjustment type	Fixed

## Environment

Standards	EN/IEC 60947-2 UL 508
Product certifications	CCC Marine EAC
IP degree of protection	IP40 conforming to IEC 60529
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0819 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------