



Main

Range	Compact
Product name	Compact NSX
Product or component type	Circuit breaker
Device short name	Compact NSX400F
Device application	Distribution
Poles description	4P
Protected poles description	3t 3t + N/2 3t + 1.6 N 4t
Neutral position	Left
Network type	AC
Network frequency	50/60 Hz
[In] rated current	400 A (40 °C)
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	690 V AC 50/60 Hz
Breaking capacity code	F (36 kA) AC
Breaking capacity	10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 600 V AC 50/60 Hz conforming to UL 508 35 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508
[Ics] rated service breaking capacity	Ics 10 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 10 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 25 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 30 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 36 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Utilisation category	Category A
Trip unit name	Micrologic 5.3 A
Trip unit technology	Electronic
Trip unit protection functions	LSI
Trip unit rating	400 A (40 °C)
Protection type	Overload protection (long time) L Instantaneous short-circuit protection I Short time short-circuit protection S
Pollution degree	3 conforming to IEC 60664-1

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Auxiliary contact composition	Without
Mechanical durability	15000 cycles
Electrical durability	12000 cycles 440 V In/2 conforming to IEC 60947-2 3000 cycles 690 V In conforming to IEC 60947-2 6000 cycles 440 V In conforming to IEC 60947-2 6000 cycles 690 V In/2 conforming to IEC 60947-2
Connection pitch	45 mm
Local signalling	LED ready LED 105 % Ir LED 90 % Ir
Neutral protection setting	0.5 x Ir 3t + N/2 1 x Ir 4t 1.6 x Ir 3t + OSN No protection 3t
Long time pick-up adjustment type Ir	Adjustable
Long time pick-up adjustment range	100...400 A
Long time delay adjustment type	Adjustable
[Tr] long-time delay adjustment range	15...400 s 1.5 x Ir 0.35...11 s 7.2 x Ir 0.5...16 s 6 x Ir
Thermal memory	20 minutes before and after tripping
Short-time pick-up adjustment type I _{sd}	Adjustable
[I _{sd}] short-time pick-up adjustment range	1.5...10 x Ir
Short-time delay adjustment type	Adjustable
[T _{sd}] short-time delay adjustment range	0...0.4 s
Instantaneous pick-up adjustment type I _i	Adjustable
Instantaneous pick-up adjustment range	1.5...12 x In
Zone selective interlocking ZSI	With
Communication of data	Instantaneous and demand values Energy metering Time-stamped histories and event tables Maximeters/minimeters Demand current and power Maintenance indicators Protection and alarm settings Power quality
Display type	LCD display

Type of measurement	Ammeter
Electrical data recording	Maintenance indicators
Height	255 mm
Width	185 mm
Depth	110 mm
Product weight	7.9 kg

Environment

Overvoltage category	Class II
Electrical shock protection class	Class II
Standards	UL 508 EN/IEC 60947
Product certifications	CCC EAC Marine
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0819 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------