

# Product data sheet

Specifications



circuit breaker, VigiComPact  
NSX400F, 36kA at 415VAC,  
MicroLogic 2.3 trip unit, 400A, add-  
on Vigi MB module, 3P 3d

LV432731

⚠ Discontinued on: Mar 30, 2022

⚠ Discontinued

## Main

Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX400...630
Device Short Name	VigiCompact NSX400F
Product Or Component Type	Circuit breaker with Vigi add-on
Device Application	Distribution
Number Of Poles	3P
Protected Poles Description	3t
[In] Rated Current	400 A at 40 °C
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 240 V AC 50/60 Hz conforming to UL 508 25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 480 V AC 50/60 Hz conforming to UL 508 20 kA at 600 V AC 50/60 Hz conforming to UL 508 20 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	F 36 kA 415 V AC
Trip Unit Name	MicroLogic 2.3
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LSol
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

## Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Ics] Rated Service Short-Circuit Breaking Capacity</b>	40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 30 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
<b>Mechanical Durability</b>	15000 cycles
<b>Electrical Durability</b>	3000 cycles at 690 V In 6000 cycles at 690 V In/2 6000 cycles at 440 V In 12000 cycles at 440 V In/2
<b>Mounting Support</b>	Backplate
<b>Upside Connection</b>	Front
<b>Downside Connection</b>	Front
<b>Connection Pitch</b>	45 mm
<b>Protection Type</b>	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
<b>Trip Unit Rating</b>	400 A at 40 °C
<b>Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)</b>	Adjustable 9 settings
<b>[Ir] Long-Time Protection Pick-Up Adjustment Range</b>	160...400 A
<b>Long-Time Protection Delay Adjustment Type Tr</b>	Fixed
<b>[Tr] Long-Time Protection Delay Adjustment Range</b>	16 s at 6 x Ir
<b>Thermal Memory</b>	20 minutes before and after tripping
<b>Short-Time Protection Pick-Up Adjustment Type Isd</b>	Adjustable 9 settings
<b>[Isd] Short-Time Protection Pick-Up Adjustment Range</b>	1.5...10 x Ir
<b>Short-Time Protection Delay Adjustment Type Tsd</b>	Fixed
<b>Instantaneous Protection Pick-Up Adjustment Type Ii</b>	Fixed
<b>[Ii] Instantaneous Protection Pick-Up Adjustment Range</b>	4800 A
<b>Earth-Leakage Protection</b>	With
<b>Earth-Leakage Add-On Module Name</b>	MB
<b>Earth-Leakage Protection Class</b>	Class A
<b>Earth-Leakage Protection Sensitivity Adjustment Type Iōn</b>	Fixed
<b>[Iōn] Earth-Leakage Protection Sensitivity Adjustment Range</b>	0.3 A
<b>Earth-Leakage Protection Time Delay Adjustment Type Δt</b>	Adjustable 4 settings
<b>Zone Selective Interlocking Zsi</b>	Without
<b>Number Of Slots For Electrical Auxiliaries</b>	7 slot(s)
<b>Local Signalling</b>	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload
<b>Width (W)</b>	135 mm
<b>Height (H)</b>	355 mm
<b>Depth (D)</b>	110 mm
<b>Net Weight</b>	6.05 kg

## Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Eu Rohs Directive Compliant  
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information