

Product data sheet

Specifications



Circuit breaker, ComPact NSX630N, 50kA/415VAC, MicroLogic 5.3A trip unit 630A, 3 poles 3d

LV432899

⚠ Discontinued on: Sep 16, 2021

⚠ Discontinued

Main

Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX400...630
Device Short Name	NSX630N
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	3P
Protected Poles Description	3t
[In] Rated Current	630 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	85 kA at 240 V AC 50/60 Hz conforming to UL 508 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 600 V AC 50/60 Hz conforming to UL 508 50 kA at 480 V AC 50/60 Hz conforming to UL 508 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	N 50 kA 415 V AC
Trip Unit Name	MicroLogic 5.3 A
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LSI
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ics] Rated Service Short-Circuit Breaking Capacity	11 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 30 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 42 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	15000 cycles
Electrical Durability	2000 cycles at 690 V In 6000 cycles at 690 V In/2 4000 cycles at 440 V In 8000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	45 mm
Protection Type	L : for overload protection (long time) S : for short time short-circuit protection I : for instantaneous short-circuit protection
Trip Unit Rating	630 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	250...630 A
Long-Time Protection Delay Adjustment Type Tr	Adjustable
[Tr] Long-Time Protection Delay Adjustment Range	15...400 s at 1.5 x Ir 0.35...11 s at 7.2 x Ir 0.5...16 s at 6 x Ir
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable
[Isd] Short-Time Protection Pick-Up Adjustment Range	1.5...10 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Adjustable
[Tsd] Short-Time Protection Delay Adjustment Range	0...0.4 s
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable
[Ii] Instantaneous Protection Pick-Up Adjustment Range	1.5...11 x In
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	With
Number Of Slots For Electrical Auxiliaries	6 slot(s)
Local Signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload
Display Type	LCD display
Type Of Measurement	Ammeter
Communication Of Data	Protection and alarm settings Power quality Instantaneous and demand values Maintenance indicators Maximeters/minimeters Time-stamped histories and event tables Energy metering Demand current and power
Width (W)	140 mm

Height (H)	255 mm
Depth (D)	110 mm
Net Weight	6.2 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15 cm
Package 1 Width	15.5 cm
Package 1 Length	29.5 cm
Package 1 Weight	5.752 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins