

Product data sheet

Specifications



Circuit breaker, VigiComPact NSX100B, 25kA/415VAC, TM-D trip unit 40A, add-on Vigi MH module, 4P 4d

LV429964

⚠ Discontinued on: Jan 8, 2021

⚠ Discontinued

Main

Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100...250
Device Short Name	VigiCompact NSX100B
Product Or Component Type	Circuit breaker with Vigi add-on
Device Application	Distribution
Number Of Poles	4P
Protected Poles Description	4t
Neutral Position	Left
[In] Rated Current	40 A at 40 °C
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	15 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	B 25 kA 415 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	LI
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ics] Rated Service Short-Circuit Breaking Capacity	20 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 7.5 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical Durability	50000 cycles
Electrical Durability	10000 cycles at 690 V In 20000 cycles at 690 V In/2 30000 cycles at 440 V In 50000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rating	40 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.7...1 x In
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	120...400 s at 1.5 x In 15 s at 6 x Ir
Short-Time Protection Pick-Up Adjustment Type Isd	Fixed
[Isd] Short-Time Protection Pick-Up Adjustment Range	500 A
Short-Time Protection Delay Adjustment Type Tsd	Fixed
Earth-Leakage Protection	With
Earth-Leakage Add-On Module Name	MH
Earth-Leakage Protection Class	Class A
Earth-Leakage Protection Sensitivity Adjustment Type Iōn	Adjustable 5 settings
[Iōn] Earth-Leakage Protection Sensitivity Adjustment Range	0.03...10 A
Earth-Leakage Protection Time Delay Adjustement Type Δt	Adjustable 4 settings
Neutral Protection Settings	1 x Ir (4t)
Number Of Slots For Electrical Auxiliaries	6 slot(s)
Width (W)	140 mm
Height (H)	236 mm
Depth (D)	86 mm
Net Weight	2.4 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262

Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	15.5 cm
Package 1 Length	24.5 cm
Package 1 Weight	3.477 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information