



## Main

Range	Compact
Product name	Compact NSX
Product or component type	Circuit breaker
Device short name	Compact NSX160B
Device application	Distribution
Poles description	3P
Protected poles description	2t
Network type	AC
Network frequency	50/60 Hz
[In] rated current	160 A ( 40 °C )
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	690 V AC 50/60 Hz
Breaking capacity code	B (25 kA) AC
Breaking capacity	25 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 15 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	Ics 15 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 20 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 25 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 40 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Utilisation category	Category A
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	LI
Trip unit rating	80 A ( 40 °C )
Protection type	Overload protection (thermal) L

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Short-circuit protection (magnetic) I

Pollution degree	3 conforming to IEC 60664-1
------------------	-----------------------------

## Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	40000 cycles
Electrical durability	10000 cycles 440 V In/2 conforming to IEC 60947-2 15000 cycles 690 V In/2 conforming to IEC 60947-2 20000 cycles 440 V In conforming to IEC 60947-2 7500 cycles 690 V In conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	Positive contact indication
Long time pick-up adjustment type Ir	Adjustable
Long time pick-up adjustment range	0.7...1 x In
Long time delay adjustment type	Fixed
[Tr] long-time delay adjustment range	15 s 6 x Ir 120...400 s 1.5 x In
Short-time pick-up adjustment type Isd	Fixed
[Isd] short-time pick-up adjustment range	640 A
Short-time delay adjustment type	Fixed
Height	161 mm
Width	105 mm
Depth	86 mm
Product weight	2.2 kg

## Environment

Overvoltage category	Class II
Electrical shock protection class	Class II
Standards	EN/IEC 60947
Product certifications	CCC Marine EAC
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0819 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------