

Product data sheet

Specifications



Circuit breaker, ComPact NSX250R, 200kA/415VAC, MicroLogic 6.2E trip unit 100A, 3 poles 3d

LV433524

Discontinued on: Jun 30, 2023

Discontinued

Important message: This product has been switched to new ComPacT range and is no longer commercialized.

Main

Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100...250
Device Short Name	NSX250R
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	3P
Protected Poles Description	3t
[In] Rated Current	100 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	200 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 80 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 45 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	R 200 kA 415 V AC
Trip Unit Name	MicroLogic 6.2 E
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LSIG
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Uij] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ics] Rated Service Short-Circuit Breaking Capacity	200 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 80 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 45 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	20000 cycles
Electrical Durability	5000 cycles at 690 V In 10000 cycles at 690 V In/2 10000 cycles at 440 V In 20000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	L : for overload protection (long time) S : for short time short-circuit protection I : for instantaneous short-circuit protection G : for ground fault protection
Trip Unit Rating	100 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	40...100 A
Long-Time Protection Delay Adjustment Type Tr	Adjustable
[Tr] Long-Time Protection Delay Adjustment Range	15...400 s at 1.5 x Ir 0.35...11 s at 7.2 x Ir 0.5...16 s at 6 x Ir
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable
[Isd] Short-Time Protection Pick-Up Adjustment Range	1.5...15 x In
Short-Time Protection Delay Adjustment Type Tsd	Adjustable 5 settings
[Tsd] Short-Time Protection Delay Adjustment Range	0...0.4 s
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable
[Ii] Instantaneous Protection Pick-Up Adjustment Range	1.5...15 x In
Ground-Fault Protection Pick-Up Adjustment Type Ig	Adjustable 9 settings
[Ig] Ground-Fault Protection Pick-Up Adjustment Range	0.4...1 x In for In = 40 A 0.2...1 x In for In > 40 A Ig enable on/off
Ground-Fault Protection Time Delay Adjustment Type Tg	Adjustable
[Tg] Ground-Fault Protection Time Delay Adjustment Range	0...0.4 s I²t=off 0.1...0.4 s I²t=on
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	With
Number Of Slots For Electrical Auxiliaries	5 slot(s)
Local Signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload
Display Type	LCD display
Type Of Measurement	Energy meter

Communication Of Data	Maximeters/minimeters Time-stamped histories and event tables Instantaneous and demand values Demand current and power Maintenance indicators Power quality Protection and alarm settings Energy metering
Width (W)	105 mm
Height (H)	161 mm
Depth (D)	86 mm
Net Weight	2.4 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	10.8 cm
Package 1 Length	19.2 cm
Package 1 Weight	2.11 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

California Proposition 65

WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov