



Main

Range	Compact
Product name	Compact NSX
Product or component type	Circuit breaker with Vigi add-on
Device short name	VigiCompact NSX250F
Device application	Distribution
Poles description	4P
Protected poles description	3t + N/2 3t 4t
Neutral position	Left
Network type	AC
Network frequency	50/60 Hz
[In] rated current	250 A (40 °C)
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	440 V AC 50/60 Hz
Breaking capacity code	F (36 kA) AC
Breaking capacity	8 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 15 kA at 600 V AC 50/60 Hz conforming to UL 508 35 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508
[Ics] rated service breaking capacity	Ics 22 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 30 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 35 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 36 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 8 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 85 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Utilisation category	Category A
Trip unit name	Micrologic 2.2
Trip unit technology	Electronic
Trip unit protection functions	LSol
Trip unit rating	100 A (40 °C)
Protection type	Overload protection (long time) L Short time short-circuit protection with fixed delay So Instantaneous short-circuit protection I
Earth-leakage add-on module name	MH
Pollution degree	3 conforming to IEC 60664-1

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	20000 cycles
Electrical durability	10000 cycles 440 V In conforming to IEC 60947-2 10000 cycles 690 V In/2 conforming to IEC 60947-2 20000 cycles 440 V In/2 conforming to IEC 60947-2 5000 cycles 690 V In conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	LED 105 % Ir LED 90 % Ir LED ready
Neutral protection setting	0.5 x Ir 3t + N/2 1 x Ir 4t No protection 3t
Long time pick-up adjustment type Ir	Adjustable 9 settings
Long time pick-up adjustment range	0.9...1 x Io
Long time delay adjustment type	Fixed
[Tr] long-time delay adjustment range	11 s 7.2 x Ir 16 s 6 x Ir 400 s 1.5 x Ir
Thermal memory	20 minutes before and after tripping
Short-time pick-up adjustment type Isd	Adjustable 9 settings
[Isd] short-time pick-up adjustment range	1.5...10 x Ir
Short-time delay adjustment type	Fixed
Instantaneous pick-up adjustment type Ii	Fixed
Instantaneous pick-up adjustment range	1500 A
Earth-leakage protection class	Class A
Earth-leakage protection	With
Residual earth-leakage sensitivity adjustment type	Adjustable 5 settings
[IΔn] residual earth-leakage sensitive adjustment	0.03...10 A
Residual earth-leakage time delay adjustment type	Adjustable 4 settings
Height	236 mm
Width	140 mm
Depth	86 mm
Product weight	2.8 kg

Environment

Overvoltage category	Class II
Electrical shock protection class	Class II
Standards	EN/IEC 60947 UL 508
Product certifications	EAC Marine CCC
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------