



Main

Range	Compact
Range of product	NSX400...630
Product or component type	Basic frame
Device short name	Compact NSX630H
Device application	Distribution
Circuit breaker name	Compact NSX630H
Poles description	4P
Neutral position	Left
Network type	AC
Network frequency	50/60 Hz
[In] rated current	630 A (40 °C)
[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	H
Breaking capacity	50 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 600 V AC 50/60 Hz conforming to UL 508 65 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Utilisation category	Category A
Pollution degree	3 conforming to IEC 60947-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Protection type	Without protection
Mechanical durability	15000 cycles conforming to IEC 60947-2
Electrical durability	2000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 4000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 6000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 8000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Connection pitch	45 mm
Height	255 mm
Width	185 mm
Depth	110 mm

Environment

Standards	IEC 60947-2 UL 508 EN 60947-2
Product certifications	CSA UL
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0819 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------