



Main

Range	Compact
Product name	Compact NSX
Product or component type	Circuit breaker
Device short name	Compact NSX630H
Device application	Motor
Poles description	3P
Protected poles description	3t
Network type	AC
Network frequency	50/60 Hz
[In] rated current	500 A (65 °C) 630 A (40 °C)
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	690 V AC 50/60 Hz
Breaking capacity code	H (70 kA) AC
Breaking capacity	50 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 600 V AC 50/60 Hz conforming to UL 508 65 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508
[Ics] rated service breaking capacity	Ics 10 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 100 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2 Ics 11 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 50 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 65 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 70 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Utilisation category	Category A
Trip unit name	Micrologic 1.3 M
Trip unit technology	Electronic
Trip unit protection functions	I
Trip unit rating	500 A (65 °C)
Protection type	Short-circuit protection (magnetic) I
Pollution degree	3 conforming to IEC 60664-1

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	15000 cycles
Electrical durability	2000 cycles 690 V In conforming to IEC 60947-2 4000 cycles 440 V In conforming to IEC 60947-2 6000 cycles 690 V In/2 conforming to IEC 60947-2 8000 cycles 440 V In/2 conforming to IEC 60947-2
Connection pitch	45 mm
Local signalling	LED ready
Short-time pick-up adjustment type Isd	Adjustable 9 settings
[Isd] short-time pick-up adjustment range	2500 A 3000 A 3500 A 4000 A 4500 A 5000 A 5500 A 6000 A 6500 A
Short-time delay adjustment type	Fixed
Instantaneous pick-up adjustment type li	Fixed
Instantaneous pick-up adjustment range	6500 A
Height	255 mm
Width	140 mm
Depth	110 mm
Product weight	6.2 kg

Environment

Overvoltage category	Class II
Electrical shock protection class	Class II
Standards	EN/IEC 60947 UL 508
Product certifications	CCC Marine EAC
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0839 - Schneider Electric declaration of conformity

[Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------