



### Main

Range	Compact
Product name	Compact NSX DC
Product or component type	Switch disconnecter
Device short name	Compact NSX1000NA DC PV
Poles description	4P
Network type	DC
[Ue] rated operational voltage	1000 V DC conforming to IEC 60947-3
[Ie] rated operational current	DC-22A: 1000 A DC 1000 V
[Ui] rated insulation voltage	1000 V DC conforming to IEC 60947-3
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-3
[Ith] conventional free air thermal current	1000 A at 65 °C
[Icm] rated short-circuit making capacity	20 kA switch-disconnector alone
Breaking capacity code	NA
Suitability for isolation	Yes conforming to IEC 60947-3
Contact position indicator	Yes
Visible break	No
Utilisation category	DC-22A
Pollution degree	3 conforming to IEC 60947-3

### Complementary

Control type	Toggle
Mounting mode	Fixed
Upside connection	Front
Downside connection	Front
[Icw] rated short-time withstand current	20 kA during 1 s conforming to IEC 60947-3
Mechanical durability	10000 cycles conforming to IEC 60947-3

Electrical durability	500 cycles 1000 V DC In conforming to IEC 60947-3
Connection pitch	70 mm
Height	327 mm
Width	280 mm
Depth	182 mm
Net weight	18 kg

## Environment

Standards	EN/IEC 60947 UL 508
Product certifications	EAC CCC
IP degree of protection	IP20 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Electrical shock protection class	Class II

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins