

# Product data sheet

Specifications



## Circuit breaker frame, MasterPact MTZ2 10H1 drawout for MicroLogic X, 1000A, 66kA/415VAC (Icu), 3P

LV848245

### Main

Range	MasterPacT
Product Name	MasterPact MTZ2
Device Short Name	MTZ2 10 H1
Product Or Component Type	Circuit breaker
Device Application	Power distribution protection
Poles Description	3P
Control Unit	Without control unit
Product Compatibility	control unit MicroLogic 2.0 X control unit MicroLogic 5.0 X control unit MicroLogic 6.0 X control unit MicroLogic 7.0 X control unit MicroLogic 2.0 Xi control unit MicroLogic 5.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 7.0 Xi
[In] Rated Current	1000 A at 40 °C
Performance Type	H1 66 kA 415 V AC
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Selectivity Category	Category B
Control Type	Push-button
Mounting Mode	Drawout

### Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	66 kA at 220/415 V AC 50/60 Hz 66 kA at 440 V AC 50/60 Hz 66 kA at 500/525 V AC 50/60 Hz 66 kA at 660/690 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	66 kA at 220/415 V AC 50/60 Hz 66 kA at 440 V AC 50/60 Hz 66 kA at 500/525 V AC 50/60 Hz 66 kA at 660/690 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	66 kA 0.5 s 66 kA 1 s 36 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	145 kA 220/415 V AC at 50/60 Hz 145 kA 440 V AC at 50/60 Hz 145 kA 500/525 V AC at 50/60 Hz 145 kA 660/690 V AC at 50/60 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sensor Rating	400 A 630 A 800 A 1000 A
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	150 W
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Mounting Support	Rails Base plate
Upside Connection	Front Rear
Downside Connection	Front Rear
Connection Pitch	115 mm
Mechanical Durability	25000 cycles with periodic preventive maintenance
Electrical Durability	10000 cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10000 cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-23A: 10000 cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-23A: 10000 cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440/690 V AC 50/60 Hz conforming to EN/IEC 60947-3
Height	Drawout circuit breaker with chassis: 439 mm Drawout circuit breaker without chassis: 300 mm
Width	Drawout circuit breaker with chassis: 441 mm Drawout circuit breaker without chassis: 378 mm
Depth	Drawout circuit breaker with chassis: 403 mm Drawout circuit breaker without chassis: 300 mm
Net Weight	90 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-2 Annex H IEC 61557-12
Product Certifications	CE IECEE CB Scheme

## Environment

Ip Degree Of Protection	IP30 conforming to EN 60529
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	0...2000 m without derating 2000...5000 m with derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.5 cm
Package 1 Width	30.5 cm
Package 1 Length	37.5 cm

---

Package 1 Weight	47.036 kg
------------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>