


Product data sheet

Specifications



TeSys F - specific contactor coil - 120...127 V AC 40...400 Hz low consumption

LX9FH1272

 To be discontinued on: Dec 31, 2028

 To be discontinued

Main

Range	TeSys
Product Or Component Type	Specific contactor coil
Device Short Name	LX9FH
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F265 LC1F330
Control Circuit Type	AC at 40...400 Hz low consumption
[Uc] Control Circuit Voltage	120...127 V AC 40...400 Hz
Average Resistance	22.9 Ohm inrush at 20 °C 516 Ohm holding at 20 °C
Operating Time	25 ms opening 45 ms closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h 55 °C

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.35...0.55 Uc (at 55 °C)
Inrush Power In Va	560...660 VA 40...400 Hz (at 20 °C)
Hold-In Power Consumption In Va	8...10 VA 40...400 Hz (at 20 °C)
Heat Dissipation	8.4...10.4 W

Environment

Ambient Air Temperature For Operation	-5...55 °C
Net Weight	0.75 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.05 cm
Package 1 Width	10.67 cm
Package 1 Length	9.4 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	0.87 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	11.213 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information