



MGN61505 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

## Main

Range	Multi 9
Product name	Multi 9 C60H-DC
Product or component type	Miniature circuit-breaker
Device short name	C60H-DC
Device application	Distribution
Poles description	1P
Number of protected poles	1
[In] rated current	5 A at 25 °C
Network type	DC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	Icu 10 kA at 220 V DC conforming to EN/IEC 60947-2 Icu 6 kA at 250 V DC conforming to EN/IEC 60947-2 Icu 20 kA at 110 V DC conforming to EN/IEC 60947-2 AIR 5 kA at 12...250 V DC conforming to UL 1077 Icu 10 kA at 220 V DC conforming to GB 14048.2 Icu 6 kA at 250 V DC conforming to GB 14048.2 Icu 20 kA at 110 V DC conforming to GB 14048.2
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

## Complementary

[Ue] rated operational voltage	12...250 V DC
Magnetic tripping limit	8.5 x In +/- 20 % AC
[Ics] rated service breaking capacity	15 kA 75 % x Icu at 110 V DC conforming to EN/IEC 60947-2 15 kA 75 % x Icu at 110 V DC conforming to GB 14048.2 7.5 kA 75 % x Icu at 250 V DC conforming to EN/IEC 60947-2 4.5 kA 75 % x Icu at 220 V DC conforming to EN/IEC 60947-2 7.5 kA 75 % x Icu at 250 V DC conforming to GB 14048.2 4.5 kA 75 % x Icu at 220 V DC conforming to GB 14048.2
Limitation class	3 conforming to EN/IEC 60947-2

[Ui] rated insulation voltage	500 V DC conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Standard top or bottom
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	73 mm
Product weight	0.128 kg
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	3000 cycles L/R = 2 ms 6000 cycles
Provision for padlocking	Padlockable
Locking options description	In position O
Connections - terminals	Tunnel type terminal, top or bottom rigid stranded wire(s) 1...25 mm <sup>2</sup> max (AWG 18...AWG 4) Tunnel type terminal, top or bottom flexible wire(s) 1...16 mm <sup>2</sup> max (AWG 18...AWG 6) Tunnel type terminal, top or bottom flexible with ferrule wire(s) 1...16 mm <sup>2</sup> max (AWG 18...AWG 6) Tunnel type terminal, top or bottom for 2 rigid stranded wire(s) 1...10 mm <sup>2</sup> max (AWG 18...AWG 8) Tunnel type terminal, top or bottom for 2 flexible wire(s) 1...10 mm <sup>2</sup> max (AWG 18...AWG 8) Tunnel type terminal, top or bottom for 2 flexible with ferrule wire(s) 1...10 mm <sup>2</sup> max (AWG 18...AWG 8) Tunnel type terminal, top or bottom for 3 flexible stranded wire(s) 1 mm <sup>2</sup> max (AWG 18)
Wire stripping length	14 mm top or bottom
Tightening torque	2.5 N.m top or bottom
Earth-leakage protection	Without

## Environment

Standards	UL 1077 GB 14048.2 EN/IEC 60947-2
Product certifications	CCC IEC UR
IP degree of protection	IP40 for modular enclosure conforming to IEC 60529 IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-2 2 conforming to GB 14048.2
Relative humidity	95 % 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---