


has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FH
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F265 LC1F330
Control circuit type	AC at 40...400 Hz low consumption
[Uc] control circuit voltage	190 V AC 40...400 Hz
Average resistance	45.6 Ohm inrush at 20 °C 1054 Ohm holding at 20 °C
Operating time	25 ms opening 45 ms closing
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 55 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.35...0.55 Uc (at 55 °C)
Inrush power in VA	560...660 VA 40...400 Hz (at 20 °C)
Hold-in power consumption in VA	8...10 VA 40...400 Hz (at 20 °C)
Heat dissipation	8.4...10.4 W

Environment

Ambient air temperature for operation	-5...55 °C
Net weight	0.75 kg

Contractual warranty

Warranty	18 months
----------	-----------