

# Product data sheet

Specifications



## Ultra compact starter, TeSys Hybrid, 3P, 500VAC, 0.75kW at 400V, 110 to 230VAC, Spring terminal

LZ1H2X43FU

⚠ Discontinued on: Dec 29, 2022

⚠ Discontinued

### Main

Range	TeSys
Product Name	TeSys Hybrid
Device Short Name	LZ1H
Product Or Component Type	Ultra-compact starter
Motor Starter Type	Direct on line
Poles Description	3P
[Ue] Rated Operational Voltage	500 V AC
[Ie] Rated Operational Current	2.4 A at 500 V AC-51 2.4 A at 500 V AC-53A 2.4 A at 500 V AC-51 mounting side by side 2.4 A at 500 V AC-53A mounting side by side
Thermal Protection Adjustment Range	0.18...2.4 A
Motor Power Kw	0.37 kW at 220 V AC 0.65 0.37 kW at 230 V AC 0.65 0.75 kW at 380 V AC 0.65 0.75 kW at 400 V AC 0.65 0.75 kW at 415 V AC 0.65 0.75 kW at 440 V AC 0.65 1.1 kW at 500 V AC 0.65
Motor Power Hp	0.5 hp at 200 V AC 0.5 hp at 230 V AC 1 hp at 460 V AC
[Uc] Control Circuit Voltage	110...230 V AC 50/60 Hz
Thermal Overload Class	Class 10A conforming to IEC 60947-4-2

### Complementary

Auxiliary Contact Composition	1 C/O fault signalling
Control Circuit Voltage Limits	85...253 V AC
Current Consumption	<= 4 mA at 110...230 V AC
Reset	Manual Automatic reset Electrical reset
Electrical Durability	30 Mcycles
Maximum Operating Rate	120 cyc/mn AC-51 50 % ON 6 cyc/mn AC-53A 50 % ON
Mounting Mode	By clips
Mounting Support	DIN rail

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Spring clamp terminals 1 cable(s) 0.2...2.5 mm² - rigid Spring clamp terminals 1 cable(s) 0.25...2.5 mm² - flexible - with cable end Spring clamp terminals 1 cable(s) 0.2...2.5 mm² - flexible - without cable end
Certifications	CULus CE
Standards	IEC 60947-4-2 UL 60947-4-1
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Pollution Degree	2
Width	22.5 mm
Height	99 mm
Depth	114.5 mm
Net Weight	212 g

## Environment

Ip Degree Of Protection	IP20
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...65 °C without derating 65...70 °C with derating
Ambient Air Temperature For Storage	-40...80 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	11.7 cm
Package 1 Length	12.0 cm
Package 1 Weight	257.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.748 kg

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a>	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>	