

Product data sheet

Specifications



UNICA - 13A, DP Switched Socket - White

MGU5_016_WE

⚠ Discontinued on: Dec 15, 2023

⚠ Discontinued

Main

| | |
|----------------------------|-----------------------------|
| Range Of Product | Unica |
| Device Application | Power supply |
| Product Or Component Type | Switched socket |
| Device Presentation | Mechanism with fixing frame |
| Outlet Poles Configuration | 2P + E |
| Outlet Standard | European |

Complementary

| | |
|--------------------------------|--|
| Device Mounting | Flush |
| Mounting Support | Wall mounted |
| Socket Number | 1 |
| Pilot Light | Red neon indicator |
| Rated Current | 13 A |
| [Ue] Rated Operational Voltage | 250 V |
| Network Type | AC |
| Network Frequency | 50 Hz |
| Load Type | Resistive |
| Number Of Modules | 2 modules |
| Fixing Mode | By screw M3.5 |
| Fixing Center | 60.3 mm |
| Colour Tint | White |
| Contacts Material | Brass and phosphor bronze |
| Connections - Terminals | Pillar terminal |
| Terminal Identifier | L N Earth |
| Tightening Torque | 0.4 N.m |
| Clamping Connection Capacity | 2 x 4 mm ² for rigid cable(s) 2 x 4 mm ² for stranded cable(s) 2 x 4 mm ² for flexible cable(s) 3 x 2.5 mm ² for rigid cable(s) 3 x 2.5 mm ² for stranded cable(s) 3 x 2.5 mm ² for flexible cable(s) |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|--|
| Material | PC (polycarbonate): grid plate PP (polypropylene): base |
| Projecting Depth | 8 mm |
| Quantity Per Set | Set of 10 |
| Type Of Packing | Polybag |
| Embedding Depth | 35 mm |
| Depth | 15 mm |
| Width | 81 mm |
| Height | 83 mm |
| Net Weight | 0.063 kg |

Environment

| | |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature For Operation | -5...40 °C |
| Relative Humidity | 0...95 % |
| Operating Altitude | <= 2000 m |
| Ik Degree Of Protection | IK01 |
| Ip Degree Of Protection | IP20 |
| Standards | SASO 2203 BS 7671 BS 1363 |
| Environmental Characteristic | Indoor use |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.3 cm |
| Package 1 Width | 8.1 cm |
| Package 1 Length | 1.5 cm |
| Package 1 Weight | 63.0 g |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
