

# Product data sheet

Specifications



## SCHUKO socket-outlet, shutter, screwless terminals, white, Aquadesign

MTN2300-7244

! Discontinued

! Discontinued on: Mar 1, 2017

! End-of-service on: Apr 12, 2017

### Main

|                               |                              |
|-------------------------------|------------------------------|
| Aesthetic Name                | Aquadesign                   |
| Product Or Component Type     | Socket-outlet                |
| Device Presentation           | Mechanism with central plate |
| Outlet Standard               | German                       |
| Socket Additional Information | Shuttered                    |

### Complementary

|                                |                      |
|--------------------------------|----------------------|
| Outlet Poles Configuration     | 2P + E               |
| Wiring Device Mounting         | Flush                |
| Fixing Mode                    | By screws and claws  |
| Rated Current                  | 16 A                 |
| [Ue] Rated Operational Voltage | 250 V                |
| Colour Tint                    | White (RAL 1013)     |
| Connections - Terminals        | Screwless terminals  |
| Material                       | Polycarbonate glossy |

### Environment

|                         |      |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 5.3 cm   |
| Package 1 Width              | 7.6 cm   |
| Package 1 Length             | 7.6 cm   |
| Package 1 Weight             | 0.096 kg |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications