

Product data sheet

Specifications



ARGUS Smoke Detector - RF Duo - aluminium

MTN5480-1160

⚠ Discontinued on: Dec 14, 2018

⚠ Discontinued

Main

Range	ARGUS
Product Or Component Type	Smoke detector
Device Application	Early detection of smouldering fires and open fires
Colour Tint	Aluminium
Quantity Per Set	Set of 1
Type Of Packing	Carton
Market Segment	Residential

Complementary

Power Supply Type	Battery
Battery Type	Lithium 3.6 V
Battery Life	10 year(s)
Detection Type	Smoke
Device Composition	2 screws 2 wall plugs
Number Of Devices	40
Type Of Connectivity	Wireless (868 MHz)
Function Available	function button alarm memory remote alarm wired or wireless network
Number Of Device Interconnected	40
Operating Distance	<= 100 m outdoor <= 30 m indoor
Technology Type	Scattered light (Tyndall effect)
Type Of Measurement	Optic
Horn Level	85 dB at 3 m
Local Signalling	Visual: LED (red) Visual: LED (yellow) Sound: alarm
Type Of Cable	Separate twin core line
Maximum Cable Distance Between Devices	500 m total 25 m between two devices
Cable Cross Section	0.5...1.5 mm², 2 wires solid

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Wire Stripping Length	9 mm
Type Of Installation	Indoor
Device Mounting	Wall Ceiling
Fixing Mode	By screws
Diameter	112 mm
Height	49 mm
Net Weight	0.179 kg

Environment

Ambient Air Temperature For Operation	0...60 °C
Standards	EN 14604
Directives	14/01 - vfdb directive
Quality Labels	Q

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	4.5 cm
Package 1 Length	11.2 cm
Package 1 Weight	0.179 kg