



Complementary

Range of product	ARGUS presence detector
Range	ARGUS
Product or component type	Presence detector
Load type	Capacitive : : 10 A 140 µF AC Incandescent lamp: 2200 W AC Fluorescent tube: 25 1-10 V electronic ballast Low voltage halogen lamp with wire-wound transformer: 500 VA AC Low voltage lamps with electronic transformer: 1050 W AC 1-10 V ballast: : 50 mA
Colour tint	Polar white
Colour code	RAL 9010
Type of packing	Carton
[Ue] rated operational voltage	220/230 V
Network frequency	50/60 Hz
Input compatibility	Push-buttons and electronic insert
[Ue] rated operational voltage	220/230 V
Input function	1 x external triggering over PL
Output current	10 A
Type of setting	Light sensitivity adjustable Time adjustment
Control type	Remote control
Function available	Master function Constant light control
Time delay	10 s...30 min
Light intensity adjustment	10...1000 lux
Horizontal detection angle	0...360 °
Detection face	Radius: 7 m
Material	PC (polycarbonate) brilliant
Device mounting	Ceiling
Mounting height	2.5 m

Environment

IP degree of protection	IP20
-------------------------	------

Ambient air temperature for operation	0...25 °C
Environmental health and issues	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
