

Product data sheet

Specifications



Room temp. ctrler 230 V w. two way
cont.&cen.pl. champagne
metallic,Sys.Des.

MTN5762-6051

⚠ Discontinued on: Apr 15, 2024

⚠ Discontinued

Main

Range	Merten
Product Name	System Design
Product Or Component Type	Thermostat
Device Presentation	Mechanism with cover plate
Colour Tint	Champagne

Complementary

Device Mounting	Flush
Fixing Mode	By screws
Device Application	Room
Technology Type	Electromechanical
Product Specific Application	Heating and cooling
Function Available	With bimetal sensor With thermal feedback
Hysteresis	0.5 K
Contacts Type And Composition	1 C/O
[In] Rated Current	10 A (on resistive load load) 4 A (on inductive load load) cos phi = 0.6
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Terminals	8 screwless terminals
Material	Metal
Ip Degree Of Protection	IP20
Height	71 mm
Width	71 mm
Depth	41 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.0 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	99.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	40
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.365 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation