

# Product data sheet

Specifications



EasyLogic PM2130, Power & Energy meter, up to the 31st harmonic, LED display, RS485, class 0.5S

METSEPM2130

## Main

Range	EasyLogic
Product Name	EasyLogic PM2100
Device Short Name	PM2130
Product Or Component Type	Power meter

## Complementary

Device Application	Sub billing Power monitoring
Power Quality Analysis	total harmonic distortion up to the 31st harmonic
Type Of Measurement	Apparent power min/max, total Active and reactive power min/max, total Current min/max, avg Voltage min/max, avg Frequency min/max, avg Total current harmonic distortion THD (I) per phase Total voltage harmonic distortion THD (U) per phase Power factor min/max, avg Apparent energy total Active and reactive energy total
Metering Type	Peak demand currents Active power P, P1, P2, P3 Demand power P, Q, S Reactive power Q, Q1, Q2, Q3 Apparent power S, S1, S2, S3 Active, reactive, apparent energy (signed, four quadrant) Voltage U, U21, U32, U13, V, V1, V2, V3 Current I, I1, I2, I3 Calculated neutral current Unbalance current Peak demand power PM, QM, SM
Accuracy Class	Class 1 reactive energy conforming to IEC 62053-24 Class 0.5S active energy conforming to IEC 62053-22 Class 5 harmonic distortion (I THD & U THD)
Measurement Accuracy	Apparent power +/- 0.5 % Active energy +/- 0.5 % Reactive energy +/- 1 % Active power +/- 0.5 % Voltage +/- 0.5 % Power factor +/- 0.01 Current +/- 0.5 % Frequency +/- 0.05 %
Measurement Current	5...6000 mA
Measurement Voltage	35...480 V AC 50/60 Hz between phases 20...277 V AC 50/60 Hz between phase and neutral 480...999000 V AC 50/60 Hz with external VT
Frequency Measurement Range	45...65 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Us] Rated Supply Voltage</b>	80...277 V AC 45...65 Hz +/- 10 % 100...277 V DC +/- 10 %
<b>Network Frequency</b>	50 Hz 60 Hz
<b>Ride-Through Time</b>	50 ms 120 V AC typical 50 ms 230 V AC typical 50 ms 125 V DC typical
<b>[In] Rated Current</b>	1 A 5 A
<b>Maximum Power Consumption In Va</b>	8 VA at 277 V AC
<b>Maximum Power Consumption In W</b>	3.3 W (power lines (AC)) 3.3 W at 277 V (power lines (DC))
<b>Input Impedance</b>	Current (impedance <= 0.3 mOhm) Voltage (impedance > 5 MOhm)
<b>Tamperproof Of Settings</b>	Protected by access code
<b>Display Type</b>	7 segments LED
<b>Display Colour</b>	Red
<b>Messages Display Capacity</b>	3 fields of 4 characters
<b>Display Digits</b>	12 digit(s) - 14.2 mm in height
<b>Demand Intervals</b>	Configurable from 1 to 60 min
<b>Information Displayed</b>	Demand current (past value) Demand current (present value) Demand power (past value) Demand power (present value) Voltage Current Frequency Energy consumption Harmonic distortion Power factor Active power Apparent power Reactive power Unbalanced in %
<b>Control Type</b>	3 x button
<b>Local Signalling</b>	Red LED: output signal 1...9999000 pulse/ k_h (kWh, kVAh, kVARh) Green LED: module operation and integrated communication
<b>Number Of Inputs</b>	0
<b>Number Of Outputs</b>	0
<b>Communication Port Protocol</b>	Modbus RTU at 4800 bps, 9600 bps, 19200 bps, 38.4 Kbps even/odd or none - 2 wires, insulation 2500 V
<b>Communication Port Support</b>	Screw terminal block: RS485
<b>Data Recording</b>	Power logs Time stamping Energy consumption logs Min/max for 8 parameters
<b>Function Available</b>	Real time clock
<b>Sampling Rate</b>	64 samples/cycle
<b>Cybersecurity</b>	Enable/disable communication ports
<b>Communication Service</b>	Remote monitoring

Product Certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1 CULus conforming to CSA C22.2 No 61010-1 RCM EAC C-Tick
Mounting Mode	Clip-on
Mounting Position	Vertical
Mounting Support	Framework
Provided Equipment	1 x installation guide
Measurement Category	Category III 480 V Category II 480...600 V
Electrical Insulation Class	Class II Double insulation
Flame Retardance	V-0 conforming to UL 94
Connections - Terminals	Current transformer: screw connection (bottom) 6 Voltage inputs: screw connection (top) 4
Material	Polycarbonate
Width	96 mm
Depth	76.09 mm total: 61.64 mm embedded:
Height	96 mm
Net Weight	300 g
Compatibility Code	PM2130

## Environment

Service Life	7 year(s)
Ip Degree Of Protection	IP54 front: conforming to IEC 60529 IP30 body: conforming to IEC 60529
Relative Humidity	5...95 % at 50 °C
Pollution Degree	2
Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Operating Altitude	<= 2000 m
Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Emission tests conforming to FCC part 15 class A
Overvoltage Category	III

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.500 cm
Package 1 Width	12.000 cm

Package 1 Length	12.500 cm
Package 1 Weight	407.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.726 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>